

Rated Impulse Withstand Voltage: 2500 V

Material

Version: 2 to 8 poles
Molding: Polyamide, self extinguishing UL 94, V-0, color grey
Temperature limits:
Short Time: 140°C (284°F)
Continuous: RTI 105°C (221°F)
Low Limit: -40°C (-40°F)
Comparative Tracking Index: CTI > 600
Oxygen Index Rating: 32%

Version: 9 to 32 poles
Molding: Polyamide (glass fiber reinforced), self extinguishing UL 94, V-0, color grey
Temperature limits:
Short Time: 200°C (392°F)
Continuous: RTI 105°C (221°F)
Low Limit: -40°C (-40°F)
Comparative Tracking Index: CTI > 175
Oxygen Index Rating: 33%

Terminal Body: Tin plated copper alloy
Wire Protector: Tin plated copper alloy
Screw: M2.6, Slotted head, zinc plated blue passivated, steel substrate
Solder Pin: Ø1.0 mm (0.04 in.), Tin plated copper alloy

Item **940 (-DS)**

Options

☐ *Only Consecutive Numbering (hot stamped numbers)*

WIRE PROTECTOR:	POLES:
with: - DS	02 to 32
	/

940

Ordering Note: Voltage rating for 0.4 in. spacing is UL certified for 15A - 300V / B and for 10A - 300V / D (942 (-DS)).

Ordering Note: Voltage rating for 0.4 in. spacing is UL certified for 15A - 300V / B and for 10A - 300V / D (942 (-DS)).

Accessories

940

WIRE PROTECTOR:
with: - DS

/

POLES:
02 to 32