


# Detailed Specifications & Technical Data



## ENGLISH MEASUREMENT VERSION

## 1084A Triad - 300V Power-Limited Tray Cable



For more Information  
please call

1-800-Belden1



### General Description:

20 AWG triads stranded (7x28) bare copper conductors, twisted triads, PVC insulation, individually shielded plus an overall Beldfoil shield (100% coverage), PVC jacket.

### Physical Characteristics (Overall)

#### Conductor

AWG:

# Conductors	# Triads	AWG	Stranding	Conductor Material
1	8	20	7x28	BC - Bare Copper

Total Number of Conductors: 25

#### Insulation

Insulation Material:

Insulation Material
PVC - Polyvinyl Chloride

#### Communication Wire

Communication Wire AWG: 22

Communication Wire Material: BC - Bare Copper

Communication Wire Stranding: 7x30

#### Inner Shield

Inner Shield Material:

Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Inner Shield Drain Wire AWG:

AWG
22

Inner Shield Drain Wire Stranding: 7x30

Inner Shield Drain Wire Conductor Material: TC - Tinned Copper

Inner Shield Color Code Chart:

Number	Color
1	Black & White & Red and Numbered 1
2	Black & White & Red and Numbered 2
3	Black & White & Red and Numbered 3
4	Black & White & Red and Numbered 4
5	Black & White & Red and Numbered 5
6	Black & White & Red and Numbered 6
7	Black & White & Red and Numbered 7
8	Black & White & Red and Numbered 8
9	Black & White & Red and Numbered 9
10	Black & White & Red and Numbered 10
11	Black & White & Red and Numbered 11
12	Black & White & Red and Numbered 12
Communication Wire	Orange

#### Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
20	7x28	TC - Tinned Copper

#### Outer Jacket

Outer Jacket Material:

# Detailed Specifications & Technical Data



## ENGLISH MEASUREMENT VERSION

## 1084A Triad - 300V Power-Limited Tray Cable

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	.064

Outer Jacket Ripcord: Yes

### Overall Cable

Overall Nominal Diameter: 0.575 in.

### Mechanical Characteristics (Overall)

Operating Temperature Range: -30°C To +105°C

UL Temperature Rating: 105°C

Bulk Cable Weight: 215 lbs/1000 ft.

Max. Recommended Pulling Tension: 432 lbs.

Min. Bend Radius/Minor Axis: 5.750 in.

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMG, ITC-ER, PLTC-ER

CEC/C(UL) Specification: CMG

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 04/01/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

### Flame Test

UL Flame Test: UL1685 FT4 Loading

C(UL) Flame Test: FT4

IEEE Flame Test: 1202

### Suitability

Suitability - Indoor: Yes

Suitability - Outdoor: Yes

Suitability - Burial: Yes

Sunlight Resistance: Yes

### Plenum/Non-Plenum

Plenum (Y/N): No

### Surface Printing (Overall)

### Electrical Characteristics (Overall)

#### Nom. Inductance:

Inductance (μH/ft)
.19

#### Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)
55

#### Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
30

#### Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
9.5

#### Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
19

# Detailed Specifications & Technical Data



## ENGLISH MEASUREMENT VERSION

## 1084A Triad - 300V Power-Limited Tray Cable

### Max. Operating Voltage - UL:

Voltage
300 V RMS

### Max. Recommended Current:

Current
3 Amps per conductor @ 25°C

### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1084A 0107500	7,500 FT	1,927.500 LB	BLACK	C Z	8 SH TRP #20 +1 #22 PVC FS PVC

### Notes:

C = CRATE REEL PUT-UP.

Z = FINAL PUT-UP LENGTH MAY VARY (+ OR -) 10% FOR SPOOLS OR REELS AND(+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

Revision Number: 1 Revision Date: 01-05-2015

© 2015 Belden, Inc.  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages, (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.