

NUMBER C-176296





METRIC

三角法 (3rd ANGLE PROJECTION)

単位: mm DIMENSIONS IN MM. DO NOT SCALE PRINT

PRINT DIST

AMP-J
REV. 10/83



パネル取付寸法 FIG 1
(RECOMMENDED PANEL OPENING DIMENSION)

- NOTES:
1. PRODUCT SPEC. 108-5302
 2. APPLICABLE CONTACT P/N
TAB CONTACT: 175150-□ (K*20-#16AWG)
175149-□ (K*26-#22AWG)
 3. MATING CONN. P/N
PLUG HSG: 176275-□
REC CONTACT: 175152-□ (K*20-#16AWG)
175151-□ (K*26-#22AWG)
 4. INSTRUCTION SHEET: IS-503J
 5. APPLICABLE PANEL THICKNESS: 0.8-2.0 (SEE FIG 1)
 6. INSERT CONN. FROM PRESS DIRECTION SIDE FOR METAL PANEL.
 7. EDGE OF THICKNESS WAY MUST NOT ROUND FOR MOLDED PANEL.

- 注:
1. 適用製品規格: 108-5302
 2. 適用コネクタ型番
タブ・コネクタ: 175150-□ (K*20-#16AWG)
175149-□ (K*26-#22AWG)
 3. 適合相手側製品型番
プラグ・ハウジング: 176275-□
リセ・コネクタ: 175152-□ (K*20-#16AWG)
175151-□ (K*26-#22AWG)
 4. 取扱説明書: IS-503J
 5. 適用パネル厚: 0.8-2.0 (FIG 1参照)
 6. 金属パネルの場合、コネクタ取付方向をパンチ加工方向にしてください。
 7. プラスチック、パネルの場合、大端部にRなき様御配慮ください。

				Copyright ©19 年 東京エー・エム・ピー株式会社				Copyright ©19__ AMP (Japan), LTD. ALL RIGHTS RESERVED.				AMP 東京エー・エム・ピー株式会社 Tokyo, Japan							
				適合電線範囲 (WIRE RANGE) mm ² (AWG -)				絶縁外径 (INSULATION DIA.) mmφ				名称 (NAME) AMPユニバーサルパワーコネクタ 8極 3.96mmピッチ キャップ・ハウジング (パネル取付タイプ) AMP UNIVERSAL POWER CONN. 3.96mm PITCH CAP HOUSING 8 Pos (PANEL MOUNT)							
				材料 (MATERIAL) 5/6 ナイロン (UL94V-0) 5/6 NYLON (UL94V-0)				仕上 (FINISH) —				一般公衆							
B	改訂	FJ00-4512-96	2/21	M.S.D.	4/12 '90	DR. 4/12 '90 Y. NARISAWA				DE. 4/12 '90 M. SHINDO				10以下: ±0.2 10を超え 30以下: ±0.25 30を超え 100以下: ±0.3 角 度: ±3°					
A	改訂	(J-12865)	Y.N.M.S	11/19 '90	CHK. 11/19 '90 Y. FUJITA				APP. 11/20 '90 N. ONOUE				SIZE LOC 番号 (No.) A3 J C-176296						
O	作成	(J-12453)	Y.N.M.S	4/12 '90									尺度 (SCALE) REV. B SHEET — 1 OF 1						
LTR 変更 (REVISION RECORD)				DR CHK DATE															

(CUSTOMER DRAWING) 参 考 図 面