


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
		B		REV PER ECO 12-010940	7-31-12	CT
		C		ECO-13-004755	26MAR2013	DH
		D		ECO-14-017030	25NOV2014	MGM



- 1

MATERIAL:
CONTACT - COPPER ALLOY
HOUSING - LCP, COLOR - BLACK
- 2

FINISH:
MATING AREA: 1.27µm MIN GOLD OVER
1.27µm MIN NICKEL
- 3



FINISH:
COMPLIANT PIN AREA: 0.38µm MIN BRIGHT TIN LEAD
OVER 1.27µm MIN NICKEL
- 4

FINISH:
COMPLIANT PIN AREA: 0.38µm MIN MATTE TIN
OVER 1.27µm MIN NICKEL
- 5

- 6


DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- 7

REFERENCE APPLICATION SPEC 114-13267 FOR RECOMMENDED
PLATING THRU HOLE DIAMETER AND PLATING THICKNESS.



2 4	2000895-2
2 3	2000895-1
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS)		DWN D. BELACK 24JUN2009	TE TE Connectivity	
DIMENSIONS: mm		CHK A. TSANG 6-24-2009		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M. McALOWIS 6-24-2009	NAME Fortis Zd. 10-COLUMN, 3-PAIR, VERTICAL END MODULE ASSEMBLY	
0 PLC ±°		PRODUCT SPEC	SIZE	
1 PLC ±0.13		108-2409	CAGE CODE	
2 PLC ±0.05		APPLICATION SPEC	DRAWING NO	
3 PLC ±°		114-13267	RESTRICTED TO	
4 PLC ±°		WEIGHT ~ &weightL.2A100779	C=2000895	
ANGLES ±2°		Customer Drawing	SCALE 8:1	
FINISH -			SHEET 1 OF 2	
-			REV D	

4805 (3/11)