

3.75 REF

5.00±0.05
TYP

3.25±0.15

1.00±0.02
TYP

8.35±0.15

3.85

3.5

1.00±0.02
TYP

10.00±0.15
TYP

12.0

5.0

5.0

5.0

Ø 1.4^{+0.1}₀

Ø 0.1

RECOMMENDED PC BOARD LAYOUT

796645-3 AS SHOWN

PRELIMINARY	0.76 µm GOLD	47.0	9	3-796645-2
PRELIMINARY	0.76 µm GOLD	37.0	7	3-796645-1
PRELIMINARY	0.76 µm GOLD	32.0	6	3-796645-0
PRELIMINARY	0.76 µm GOLD	27.0	5	2-796645-9
PRELIMINARY	0.76 µm GOLD	22.0	4	2-796645-8
PRELIMINARY	0.76 µm GOLD	17.0	3	2-796645-7
PRELIMINARY	0.76 µm GOLD	42.0	8	2-796645-6
	TIN	127.0	25	2-796645-5
	TIN	122.0	24	2-796645-4
	TIN	117.0	23	2-796645-3
	TIN	112.0	22	2-796645-2
	TIN	107.0	21	2-796645-1
	TIN	102.0	20	2-796645-0
	TIN	97.5	19	1-796645-9
	TIN	92.0	18	1-796645-8
	TIN	87.0	17	1-796645-7
	TIN	82.0	16	1-796645-6
	TIN	77.0	15	1-796645-5
	TIN	72.0	14	1-796645-4
	TIN	67.0	13	1-796645-3
	TIN	62.0	12	1-796645-2
	TIN	57.0	11	1-796645-1
	TIN	52.0	10	1-796645-0
	TIN	47.0	9	796645-9
	TIN	42.0	8	796645-8
	TIN	37.0	7	796645-7
	TIN	32.0	6	796645-6
	TIN	27.0	5	796645-5
	TIN	22.0	4	796645-4
	TIN	17.0	3	796645-3
	TIN	12.0	2	796645-2
CONTACT PLATING		DIM L	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±0.2

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±

FINISH

MATERIAL

DWN S.WELDON 19OCT2000

CHK D.BIEVENOUR 19OCT2000

APVD D.BIEVENOUR 19OCT2000

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE Connectivity

NAME TERMI-BLOK HEADER ASSEMBLY, 90 DEGREE, CLOSED ENDS, 5.00mm PITCH

SIZE A2

CAGE CODE 00779

DRAWING NO C-796645

RESTRICTED TO

SCALE 4:1

SHEET 1

OF 1

REV A3

1471-9 (3/11)

Pro/ENGINEER DRAWING