

CD4023BM/CD4023BC **Buffered Triple 3-Input NAND Gate** **CD4025BM/CD4025BC** **Buffered Triple 3-Input NOR Gate**



General Description

These triple gates are monolithic complementary MOS (CMOS) integrated circuits constructed with N- and P-channel enhancement mode transistors. They have equal source and sink current capabilities and conform to standard B series output drive. The devices also have buffered outputs which improve transfer characteristics by providing very high gain. All inputs are protected against static discharge with diodes to V_{DD} and V_{SS} .

Features

- Wide supply voltage range 3.0V to 15V
- High noise immunity 0.45 V_{DD} (typ.)
- Low power TTL compatibility fan out of 2 driving 74L or 1 driving 74LS
- 5V–10V–15V parametric ratings
- Symmetrical output characteristics
- Maximum input leakage 1 μA at 15V over full temperature range

Connection Diagrams



Order Number CD4023B or CD4025B

CD4023BM/CD4023BC Buffered Triple 3-Input NAND Gate
CD4025BM/CD4025BC Buffered Triple 3-Input NOR Gate

Absolute Maximum Ratings (Notes 1 & 2)

If Military/Aerospace specified devices are required, please contact the National Semiconductor Sales Office/Distributors for availability and specifications.

DC Supply Voltage (V_{DD}) $-0.5 V_{DC}$ to $+18 V_{DC}$

Input Voltage (V_{IN}) $-0.5 V_{DC}$ to $V_{DD} + 0.5 V_{DC}$

Storage Temp. Range (T_S) -65°C to $+150^{\circ}\text{C}$

Power Dissipation (P_D)

Dual-In-Line 700 mW

Small Outline 500 mW

Lead Temperature (T_L)

(Soldering, 10 seconds) 260°C

Recommended Operating Conditions

DC Supply Voltage (V_{DD})

$5 V_{DC}$ to $15 V_{DC}$

Input Voltage (V_{IN})

$0 V_{DC}$ to $V_{DD} V_{DC}$

Operating Temperature Range (T_A)

CD4023BM, CD4025BM

-55°C to $+125^{\circ}\text{C}$


CD4023BC, CD4025BC

-40°C to $+85^{\circ}\text{C}$

DC Electrical Characteristics CD4023BM, CD4025BM (Note 2)

Symbol	Parameter	Conditions	-55°C		$+25^{\circ}\text{C}$			$+125^{\circ}\text{C}$		Units
			Min	Typ	Min	Typ	Max	Min	Max	
I_{DD}	Quiescent Device Current	$V_{DD} = 5\text{V}$		0.25		0.004	0.25		7.5	μA
		$V_{DD} = 10\text{V}$		0.5		0.005	0.5		15	μA
		$V_{DD} = 15\text{V}$		1.0		0.006	1.0		30	μA
V_{OL}	Low Level Output Voltage	$V_{DD} = 5\text{V}$		0.05		0	0.05		0.05	V
		$V_{DD} = 10\text{V}$		0.05		0	0.05		0.05	V
		$V_{DD} = 15\text{V}$		0.05		0	0.05		0.05	V
V_{OH}	High Level Output Voltage	$V_{DD} = 5\text{V}$	4.95		4.95	5		4.95		V
		$V_{DD} = 10\text{V}$	9.95		9.95	10		9.95		V
		$V_{DD} = 15\text{V}$	14.95		14.95	15		14.95		V
V_{IL}	Low Level Input Voltage	$V_{DD} = 5\text{V}, V_O = 4.5\text{V}$		1.5		2	1.5		1.5	V
		$V_{DD} = 10\text{V}, V_O = 9.0\text{V}$		3.0		4	3.0		3.0	V
		$V_{DD} = 15\text{V}, V_O = 13.5\text{V}$		4.0		6	4.0		4.0	V
V_{IH}	High Level Input Voltage	$V_{DD} = 5\text{V}, V_O = 0.5\text{V}$	3.5		3.5	3		3.5		V
		$V_{DD} = 10\text{V}, V_O = 1.0\text{V}$	7.0		7.0	6		7.0		V
		$V_{DD} = 15\text{V}, V_O = 1.5\text{V}$	11.0		11.0	9		11.0		V
I_{OL}	Low Level Output Current (Note 3)	$V_{DD} = 5\text{V}, V_O = 0.4\text{V}$	0.64		0.51	0.88		0.36		mA
		$V_{DD} = 10\text{V}, V_O = 0.5\text{V}$	1.6		1.3	2.2		0.90		mA
		$V_{DD} = 15\text{V}, V_O = 1.5\text{V}$	4.2		3.4	8		2.4		mA
I_{OH}	High Level Output Current (Note 3)	$V_{DD} = 5\text{V}, V_O = 4.6\text{V}$	-0.64		-0.51	-0.88		-0.36		mA
		$V_{DD} = 10\text{V}, V_O = 9.5\text{V}$	-1.6		-1.3	-2.2		-0.90		mA
		$V_{DD} = 15\text{V}, V_O = 13.5\text{V}$	-4.2		-3.4	-8		-2.4		mA
I_{IN}	Input Current	$V_{DD} = 15\text{V}, V_{IN} = 0\text{V}$		-0.10		-10^{-5}	-0.10		-1.0	μA
		$V_{DD} = 15\text{V}, V_{IN} = 15\text{V}$		0.10		10^{-5}	0.10		1.0	μA

Schematic Diagram



$\frac{1}{3}$ Device Shown

*All Inputs Protected
by Standard CMOS Input
Protection Circuit.

TL/F/5956-3

DC Electrical Characteristics CD4023BC, CD4025BC (Note 2)

Symbol	Parameter	Conditions	−40°C		+25°C			+85°C		Units
			Min	Typ	Min	Typ	Max	Min	Max	
I_{DD}	Quiescent Device Current	$V_{DD} = 5V$ $V_{DD} = 10V$ $V_{DD} = 15V$		1.0 2.0 4.0		0.004 0.005 0.006	1.0 2.0 4.0		7.5 15 30	μA
V_{OL}	Low Level Output Voltage	$V_{DD} = 5V$ $V_{DD} = 10V$ $V_{DD} = 15V$		0.05 0.05 0.05		0 0 0	0.05 0.05 0.05		0.05 0.05 0.05	V
V_{OH}	High Level Output Voltage	$V_{DD} = 5V$ $V_{DD} = 10V$ $V_{DD} = 15V$	4.95 9.95 14.95		4.95 9.95 14.95	5 10 15		4.95 9.95 14.95		V
V_{IL}	Low Level Input Voltage	$V_{DD} = 5V, V_O = 4.5V$ $V_{DD} = 10V, V_O = 9.0V$ $V_{DD} = 15V, V_O = 13.5V$ } $ I_O < 1\mu A$		1.5 3.0 4.0		2 4 6	1.5 3.0 4.0		1.5 3.0 4.0	V
V_{IH}	High Level Input Voltage	$V_{DD} = 5V, V_O = 0.5V$ $V_{DD} = 10V, V_O = 1.0V$ $V_{DD} = 15V, V_O = 1.5V$ } $ I_O < 1\mu A$	3.5 7.0 11.0		3.5 7.0 11.0	3 6 9		3.5 7.0 11.0		V
I_{OL}	Low Level Output Current (Note 3)	$V_{DD} = 5V, V_O = 0.4V$ $V_{DD} = 10V, V_O = 0.5V$ $V_{DD} = 15V, V_O = 1.5V$	0.52 1.3 3.6		0.44 1.1 3.0	0.88 2.2 8		0.36 0.90 2.4		mA
I_{OH}	High Level Output Current (Note 3)	$V_{DD} = 5V, V_O = 4.6V$ $V_{DD} = 10V, V_O = 9.5V$ $V_{DD} = 15V, V_O = 13.5V$	−0.52 −1.3 −3.6		−0.44 −1.1 −3.0	−0.88 −2.2 −8		−0.36 −0.90 −2.4		mA
I_{IN}	Input Current	$V_{DD} = 15V, V_{IN} = 0V$ $V_{DD} = 15V, V_{IN} = 15V$		−0.3 0.3		-10^{-5} 10^{-5}	−0.3 0.3		−1.0 1.0	μA


Note 1: "Absolute Maximum Ratings" are those values beyond which the safety of the device cannot be guaranteed; they are not meant to imply that the devices should be operated at these limits. The table of "Recommended Operating Conditions" and "Electrical Characteristics" provides conditions for actual device operation.

Note 2: $V_{SS} = 0V$ unless otherwise specified.

Note 3: I_{OH} and I_{OL} are tested one output at a time.

Schematic Diagram

CD4025BM/CD4025BC



TL/F/5956-4

AC Electrical Characteristics* $T_A = 25^{\circ}\text{C}$, $C_L = 50\text{ pF}$, $R_L = 200\text{ k}$, unless otherwise specified

Symbol	Parameter	Conditions	CD4023BC CD4023BM			CD4025BC CD4025BM			Units
			Min	Typ	Max	Min	Typ	Max	
t_{PHL}	Propagation Delay, High-to-Low Level	$V_{\text{DD}} = 5\text{V}$		130	250		130	250	ns
		$V_{\text{DD}} = 10\text{V}$		60	100		60	100	ns
		$V_{\text{DD}} = 15\text{V}$		40	70		40	70	ns
t_{PLH}	Propagation Delay, Low-to-High Level	$V_{\text{DD}} = 5\text{V}$		110	250		120	250	ns
		$V_{\text{DD}} = 10\text{V}$		50	100		60	100	ns
		$V_{\text{DD}} = 15\text{V}$		35	70		40	70	ns
t_{THL} , t_{TLH}	Transition Time	$V_{\text{DD}} = 5\text{V}$		90	200		90	200	ns
		$V_{\text{DD}} = 10\text{V}$		50	100		50	100	ns
		$V_{\text{DD}} = 15\text{V}$		40	80		40	80	ns
C_{IN}	Average Input Capacitance	Any Input		5	7.5		5	7.5	pF
C_{PD}	Power Dissipation Capacity (Note 4)	Any Gate		17			17		pF

*AC Parameters are guaranteed by DC correlated testing.

Note 4: C_{PD} determines the no load AC power consumption of any CMOS device. For complete explanation, see 54C/74C Family Characteristics Application Note AN-90.

Physical Dimensions

inches (millimeters)

The diagram shows three views of the J14A package: a top view, a side view, and a front view. The top view shows a rectangular package with pins 1-7 on the bottom and 8-14 on the top. Dimensions include a width of 0.785 inches (19.939 mm) MAX, a height of 0.220-0.310 inches (5.588-7.874 mm), and a corner radius of 0.025 inches (0.635 mm) RAD. The side view shows a package height of 0.180 inches (4.572 mm) MAX and a pin pitch of 0.060 inches (1.524 mm) ±0.005. The front view shows a package width of 0.290-0.320 inches (7.366-8.128 mm), a pin pitch of 0.018 inches (0.457 mm) ±0.003, and a pin diameter of 0.010 inches (0.254 mm) ±0.010. The package is labeled with 'GLASS SEALANT' and 'MAX BOTH ENDS'.

0.785
(19.939)
MAX

0.025
(0.635)
RAD

0.220-0.310
(5.588-7.874)

14 13 12 11 10 9 8

1 2 3 4 5 6 7

0.290-0.320
(7.366-8.128)

0.180
(4.572)
MAX

95° ±5°

10° MAX

0.310-0.410
(7.874-10.41)

0.008-0.012
(0.203-0.305)

0.098
(2.489)
MAX BOTH ENDS

0.005
(0.127)
MIN

GLASS
SEALANT

0.060 ±0.005
(1.524 ±0.127)

0.200
(5.080)
MAX

0.020-0.060
(0.508-1.524)

86°-94° TYP

0.018 ±0.003
(0.457 ±0.076)


0.100 ±0.010
(2.540 ±0.254)

0.125-0.200
(3.175-5.080)

0.150
(3.81)
MIN


Ceramic Dual-In-Line Package (J)
Order Number CD4023BMJ, CD4023BCJ, CD4025BMJ or CD4025BCJ
NS Package Number J14A

J14A (REV G)



CD4023BM/CD4023BC Buffered Triple 3-Input NAND Gate
CD4025BM/CD4025BC Buffered Triple 3-Input NOR Gate

Physical Dimensions inches (millimeters) (Continued)



Molded Dual-In-Line Package (N)
Order Number CD4023BMN, CD4023BCN, CD4025BMN or CD4025BCN
NS Package Number N14A

LIFE SUPPORT POLICY

NATIONAL'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF NATIONAL SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

 National Semiconductor Corporation 1111 West Bardin Road Arlington, TX 76017 Tel: 1(800) 272-9959 Fax: 1(800) 737-7018	National Semiconductor Europe Fax: (+49) 0-180-530 85 86 Email: cnjwge@tevm2.nsc.com Deutsch Tel: (+49) 0-180-530 85 85 English Tel: (+49) 0-180-532 78 32 Français Tel: (+49) 0-180-532 93 58 Italiano Tel: (+49) 0-180-534 16 80	National Semiconductor Hong Kong Ltd. 13th Floor, Straight Block, Ocean Centre, 5 Canton Rd. Tsimshatsui, Kowloon Hong Kong Tel: (852) 2737-1600 Fax: (852) 2736-9960	National Semiconductor Japan Ltd. Tel: 81-043-299-2309 Fax: 81-043-299-2408
---	---	--	--

National does not assume any responsibility for use of any circuitry described, no circuit patent licenses are implied and National reserves the right at any time without notice to change said circuitry and specifications.