

611/621-Series





The miniature 611/621-Series switches are double insulated and available in single or double pole. These snap-in mounting style switches are available with paddle, rocker or Visi-Rocker type actuators. A variety of terminations are offered with ratings through 11 amps. International approvals are also available.

Specifications

- Certifications*: UL, CSA, VDE, TUV, SEMKO, DEMKO, SEV, NEMKO, SETI
- Dielectric Strength: 1,000V (minimum)
- Insulation Resistance: 100 Megohms (minimum)
- Base Material: Nylon
- Actuator Material: Nylon

* Due to ongoing technological advances, consult factory for certification specifics.

Dimensional Specifications: in. [mm]



6		21		1		5		9		1		9		-		0		-		9		-		V																																																																							
SERIES		BASE/ACTUATOR COLOR ¹				RATING ²				TERMINATION ⁴				ROCKER FACE LEGEND																																																																																	
6		<table><tr><td></td><td>BASE</td><td>ACTUATOR</td></tr><tr><td>1</td><td>BLACK</td><td>BLACK</td></tr><tr><td>2</td><td>BLACK</td><td>WHITE</td></tr><tr><td>4</td><td>WHITE</td><td>BLACK</td></tr><tr><td>5</td><td>WHITE</td><td>WHITE</td></tr></table>					BASE	ACTUATOR	1	BLACK	BLACK	2	BLACK	WHITE	4	WHITE	BLACK	5	WHITE	WHITE	<table><tr><td>1</td><td>.4VA MAX @20V MAX (AC/DC)</td></tr><tr><td>2</td><td>2A 250VAC</td></tr><tr><td></td><td>5A 125VAC</td></tr><tr><td></td><td>RESISTIVE</td></tr><tr><td>3</td><td>11A 125VAC H³</td></tr><tr><td>4</td><td>4A 250 VAC</td></tr><tr><td></td><td>8A 125VAC</td></tr><tr><td>9</td><td>4A 250VAC</td></tr><tr><td></td><td>8A 125VAC</td></tr><tr><td></td><td>INDUCTIVE</td></tr><tr><td></td><td>6(4)A 250VAC T85⁸</td></tr></table>				1	.4VA MAX @20V MAX (AC/DC)	2	2A 250VAC		5A 125VAC		RESISTIVE	3	11A 125VAC H ³	4	4A 250 VAC		8A 125VAC	9	4A 250VAC		8A 125VAC		INDUCTIVE		6(4)A 250VAC T85 ⁸	<table><tr><td>1</td><td>.080 SOLDER LUG</td></tr><tr><td>2</td><td>PC TERM</td></tr><tr><td>3</td><td>WIRE LEAD⁷</td></tr><tr><td>4</td><td>WIRE LEAD</td></tr><tr><td>6</td><td>.187 SOLDER LUG</td></tr><tr><td>7</td><td>PC BACK MOUNT</td></tr><tr><td>8</td><td>PC FRONT MOUNT</td></tr><tr><td>9</td><td>.187TAB (QC)</td></tr></table>				1	.080 SOLDER LUG	2	PC TERM	3	WIRE LEAD ⁷	4	WIRE LEAD	6	.187 SOLDER LUG	7	PC BACK MOUNT	8	PC FRONT MOUNT	9	.187TAB (QC)	<table><tr><td></td><td></td><td>INK TRANSFER STAMP⁶</td></tr><tr><td>0</td><td>NO LEGEND</td><td>0</td></tr><tr><td></td><td>ON-OFF (VERTICAL)</td><td>A</td></tr><tr><td></td><td>ON-OFF (HORIZONTAL)</td><td>B</td></tr><tr><td>8</td><td>I-O (HORIZONTAL)</td><td>D</td></tr><tr><td>9</td><td>I-O (VERTICAL)</td><td>E</td></tr><tr><td></td><td>● (indicates ON) (ON ROCKER RADIUS)</td><td>F</td></tr></table>										INK TRANSFER STAMP ⁶	0	NO LEGEND	0		ON-OFF (VERTICAL)	A		ON-OFF (HORIZONTAL)	B	8	I-O (HORIZONTAL)	D	9	I-O (VERTICAL)	E		● (indicates ON) (ON ROCKER RADIUS)	F
	BASE	ACTUATOR																																																																																													
1	BLACK	BLACK																																																																																													
2	BLACK	WHITE																																																																																													
4	WHITE	BLACK																																																																																													
5	WHITE	WHITE																																																																																													
1	.4VA MAX @20V MAX (AC/DC)																																																																																														
2	2A 250VAC																																																																																														
	5A 125VAC																																																																																														
	RESISTIVE																																																																																														
3	11A 125VAC H ³																																																																																														
4	4A 250 VAC																																																																																														
	8A 125VAC																																																																																														
9	4A 250VAC																																																																																														
	8A 125VAC																																																																																														
	INDUCTIVE																																																																																														
	6(4)A 250VAC T85 ⁸																																																																																														
1	.080 SOLDER LUG																																																																																														
2	PC TERM																																																																																														
3	WIRE LEAD ⁷																																																																																														
4	WIRE LEAD																																																																																														
6	.187 SOLDER LUG																																																																																														
7	PC BACK MOUNT																																																																																														
8	PC FRONT MOUNT																																																																																														
9	.187TAB (QC)																																																																																														
		INK TRANSFER STAMP ⁶																																																																																													
0	NO LEGEND	0																																																																																													
	ON-OFF (VERTICAL)	A																																																																																													
	ON-OFF (HORIZONTAL)	B																																																																																													
8	I-O (HORIZONTAL)	D																																																																																													
9	I-O (VERTICAL)	E																																																																																													
	● (indicates ON) (ON ROCKER RADIUS)	F																																																																																													
ACTUATOR STYLE		POLES				FUNCTION				EPOXY SEALED TERMINALS																																																																																					
11 PADDLE		<table><tr><td>1</td><td>SINGLE POLE</td></tr><tr><td>2</td><td>DOUBLE POLE</td></tr><tr><td>5</td><td>DOUBLE POLE W/ HIGH BARRIERS</td></tr><tr><td>6</td><td>SINGLE POLE W/ HIGH BARRIERS</td></tr></table>				1	SINGLE POLE	2	DOUBLE POLE	5	DOUBLE POLE W/ HIGH BARRIERS	6	SINGLE POLE W/ HIGH BARRIERS	<table><tr><td>1</td><td>ON-NONE-OFF</td></tr></table>				1	ON-NONE-OFF	<table><tr><td>E</td><td>EPOXY</td></tr><tr><td>0</td><td>NONE REQUIRED</td></tr></table>				E	EPOXY	0	NONE REQUIRED																																																																				
1	SINGLE POLE																																																																																														
2	DOUBLE POLE																																																																																														
5	DOUBLE POLE W/ HIGH BARRIERS																																																																																														
6	SINGLE POLE W/ HIGH BARRIERS																																																																																														
1	ON-NONE-OFF																																																																																														
E	EPOXY																																																																																														
0	NONE REQUIRED																																																																																														
21 CURVED ROCKER																																																																																															

NOTES:

Shading indicates standard configurations.

Panel Cut-Out Recommendations: For sheet metal panels, switch must enter panel in same direction as the punch. (Burr on bottom.) Test cut hole in actual material.

1 Matte finish is standard. Custom colors are available. Consult factory.

2 Rating 1 contact surfaces: gold plate over nickel plate. Rating Code 9 available with function 1 or 2 only.

3 Available in single pole with high barriers, ON-NONE-OFF circuit with .187TAB terminals only.

4 Terminations 1, 2 and 3 are not available with function 1. Terminations 4, 6, 7, 8 and 9 are available with function 1 or 2 only.

5 Molded-in Legend available only with Visi-Rocker Option.

6 White is standard with dark actuators; black is standard with light actuators.

7 Termination 3 available with rating 2 only - 18 gauge wire used.

8 Rating 9 using Termination 1 or 2 is rated T55 only.