

Product information

M12 Single Ended Cordsets - Standard Types with LED - RKWT/LED A 4-3-224/5 M

Industrial Connecting Solutions: Circular Connectors: M8 - M12 Connectors: M12 Connectors: M12 Circular connector acc. to IEC 61076-2-101: M12 Single Ended Cordsets: M12 Single Ended Cordsets -

Standard Types with LED

http://www.e-catalog.beldensolutions.com/link/57078-24228-256281-256292-256304-58429-58479-74778/en/RKWT-04-LED_A-224-05/uistate

Name	
M12 Single Ended Cordsets - Standard Types with LED	
	
	Actuator/sensor cordset, M12 female connector, right angled version, with self-locking threaded joint and molded cable, with LED operation and function indicator, 4 poles, A circuit, PUR jacket, 5 meters
Delivery informations	
Availability	available
Product description	
Type	RKWT/LED A 4-3-224/5 M
Order No.	11478
Description	Actuator/sensor cordset, M12 female connector, right angled version, with self-locking threaded joint and molded cable, with LED operation and function indicator, 4 poles, A circuit, PUR jacket, 5 meters
Number of contacts	4
Color of housing	black translucent
Product characteristics	Vibration resistance
Classification	
Belden brand	Lumberg-Automation
Eclass-ID	27260702
Mechanical data	
Type of plug-in contact	Female connector
Design of housing	angled
Thread	M12
Design of electrical connection	connector M12
Coding of the M12 round plug connector	A
LED display present	✗
Environmental conditions	
Environmental temperature	-25 °C ... 80 °C
Degree of protection (IP), mounted	IP67
Pollution degree	3
Materials	
Housing material / Molded body	TPU
Contact bearer material	TPU
Contact material	CuSn
Contact material - Surface refinement	pre-nickel and gold-plated
Knurled screw / nut material	CuZn, nickel-plated
Sealing material	FKM
Electrical data	
Contact resistance	≤ 5 mΩ
Rated current I _n	4 A at 40°C, UL and notice derating
Nominal voltage	10 - 30 V DC
Rated voltage (Value)	32 V
Insulation resistance	> 1 GΩ
Approvals	
Approvals	UL

Belden Deutschland GmbH

Im Gewerbepark 2
58579 Schalksmühle
Germany
Phone: +49 7127/14-1806
E-Mail: icos-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.