

JC

Snap-in Terminal Type

series


- Excellent in voltage holding property.
- Suitable for quick charge and discharge.
- Wide temperature range (– 25°C to + 60°C).
- Compliant to the RoHS directive (2002/95/EC).



■ Specifications

Item	Performance Characteristics	
Category Temperature Range	– 25 to +60°C	
Rated Voltage Range	2.5V	
Rated Capacitance Range	15 to 150F See Note	
Capacitance Tolerance	± 20% (20°C)	
Leakage Current	0.5C (mA) [C : Rated Capacitance(F)] (After 30 minutes' application of rated voltage, 2.5V)	
Stability at Low Temperature	Capacitance (– 25°C) / Capacitance (+20°C) × 100 ≥ 70%	
ESR, DCR*	Refer to the list below (20°C). *DC internal resistance	
Endurance	The specifications listed at right shall be met when the capacitors are restored to 20°C after the rated voltage is applied for 2000 hours at 60°C.	Capacitance change
		Within ±30% of the initial capacitance value
		ESR
Shelf Life	The specifications listed at right shall be met when the capacitors are restored to 20°C after storing the capacitors under no load for 2000 hours at 60°C.	300% or less than the initial specified value
		Leakage current
		Less than or equal to the initial specified value
Shelf Life		Capacitance change
		Within ±30% of the initial capacitance value
		ESR
Marking	Printed with white color letter on black sleeve.	300% or less than the initial specified value
		Leakage current
		Less than or equal to the initial specified value


■ Drawing



(PC board hole dimensions)

(Terminal dimensions)

Type numbering system (Example : 2.5V 150F)



■ Dimensions

Rated Voltage (code)	Cap. (F)	Cap. code	ESR(mΩ) (at 1kHz)	DCR※ Typical (mΩ)	Case size φD×L (mm)			
					φ 22 (Z)	φ 25 (A)	φ 30 (B)	φ 35 (C)
2.5V (0E)	15	156	120	160	22×20			
	18	186	120	140		25×20		
	22	226	90	130			30×20	
	27	276	90	110	22×30		30×20	
	33	336	80	90		25×30		35×20
	39	396	80	80	22×35	25×30		35×20
	47	476	70	60	22×40	25×35		
	56	566	70	50		25×40	30×30	
	68	686	60	45				35×30
	82	826	60	35		25×50	30×40	
	100	107	50	30				35×35
	120	127	50	25			30×50	35×40
	150	157	40	22				35×50

Note :

The capacitance calculated from discharge time (ΔT) with constant current (i) after 30minute charge with rated voltage (2.5V).

The discharge current (i) is 0.01 × rated capacitance (F). The discharge time (ΔT) measured between 2V and 1V with constant current.

The capacitance calculated bellow.

$$\text{Capacitance (F)} = i \times \Delta T$$

※ The listed DCR value is typical and therefore not a guaranteed value.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Nichicon:

[JJC0E476MELA](#) [JJC0E826MELB](#) [JJC0E826MELA](#) [JJC0E686MELC](#) [JJC0E566MELB](#) [JJC0E566MELA](#)
[JJC0E476MELZ](#) [JJC0E396MELZ](#) [JJC0E396MELC](#) [JJC0E396MELA](#) [JJC0E338MSEJBN](#) [JJC0E336MELC](#)
[JJC0E336MELA](#) [JJC0E477MSECBN](#) [JJC0E157MELC](#) [JJC0E278MSEHBN](#) [JJC0E186MELA](#) [JJC0E108MSEFBN](#)
[JJC0E276MELB](#) [JJC0E228MSEHBN](#) [JJC0E226MELB](#) [JJC0E188MSEGBN](#) [JJC0E158MSEGBN](#) [JJC0E156MELZ](#)
[JJC0E128MSEFBN](#) [JJC0E127MELB](#) [JJC0E107MELC](#) [JJC0E127MELC](#) [JJC0E276MELZ](#) [JJC0E108MSEFBB](#)
[JJC0E128MSEFBB](#) [JJC0E158MSEGBB](#) [JJC0E188MSEGBB](#) [JJC0E228MSEHBB](#) [JJC0E278MSEHBB](#)
[JJC0E338MSEJBB](#) [JJC0E477MSEC](#)