





PART NAME	NEMA 4X ENCLOSURE	PART No.	PN-1328, PN-1328-C AND PN-1328-DG
-----------	-------------------	----------	-----------------------------------

INDUSTRY STANDARDS:

POLYCARBONATE (LIGHT GRAY AND CLEAR)
 UL94V-2 FLAMMABILITY RATING (UL FILE #E41613)
 UV STABILIZED
 SERVICE TEMPERATURE RANGE: -40°C TD +120°C
 ABS (DARK GRAY)
 UL94-HB FLAMMABILITY RATING (UL FILE #E56070)
 SERVICE TEMPERATURE RANGE: -40°C TD +80°C

(*) MOUNTING BOSSSES USE EITHER M2.5 METRIC DR #4 STD. SHEET METAL SCREWS x 0.188" LG. (NOT SUPPLIED)



NOTE: ALL DIMENSIONS HAVE ±0.015 TOLERANCE UNLESS OTHERWISE SPECIFIED.

PART NUMBER	BODY	COVER	BODY	COVER	HARDWARE KIT
PN-1328	POLYCARBONATE	POLYCARBONATE	LIGHT GRAY	CLEAR	M4 x 20mm (0.787") LG. SCREWS FOR ASSEMBLY
PN-1328-C	POLYCARBONATE	POLYCARBONATE	LIGHT GRAY	CLEAR	
PN-1328-DG	HIGH-IMPACT ABS	HIGH-IMPACT ABS	DARK GRAY	CLEAR	