


Features

- Epitaxial Planar Die Construction
- Complementary PNP Type Available (MMST4403)
- Ultra-Small Surface Mount Package
- Lead Free/ROHS Compliant (Note 2)**
- "Green" Device (Note 3 and 4)**

Mechanical Data

- Case: SOT-323
- Case Material: Molded Plastic, "Green" Molding Compound, Note 4. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020C
- Terminals: Solderable per MIL-STD-202, Method 208
- Terminal Connections: See Diagram
- Lead Free Plating (Matte Tin Finish annealed over Alloy 42 leadframe).
- Marking Information: K3X - See Page 4
- Ordering & Date Code Information: See Page 4
- Weight: 0.006 grams (approximate)



SOT-323		
Dim	Min	Max
A	0.25	0.40
B	1.15	1.35
C	2.00	2.20
D	0.65 Nominal	
E	0.30	0.40
G	1.20	1.40
H	1.80	2.20
J	0.0	0.10
K	0.90	1.00
L	0.25	0.40
M	0.10	0.18
α	0°	8°

All Dimensions in mm

Maximum Ratings

$\text{@ } T_A = 25^\circ\text{C}$ unless otherwise specified

Characteristic	Symbol	Value	Unit
Collector-Base Voltage	V_{CBO}	60	V
Collector-Emitter Voltage	V_{CEO}	40	V
Emitter-Base Voltage	V_{EBO}	6.0	V
Collector Current – Continuous (Note 1)	I_C	600	mA
Power Dissipation (Note 1)	P_d	200	mW
Thermal Resistance, Junction to Ambient (Note 1)	$R_{\theta JA}$	625	°C/W
Operating and Storage Temperature Range	T_j, T_{STG}	-55 to +150	°C

Notes:

1. Device mounted on FR-4 PCB, 1 inch x 0.85 inch x 0.062 inch; pad layout as shown on Diodes Inc. suggested pad layout document AP02001, which can be found on our website at <http://www.diodes.com/datasheets/ap02001.pdf>.
2. No purposefully added lead.
3. Diodes Inc.'s "Green" policy can be found on our website at http://www.diodes.com/products/lead_free/index.php.
4. Product manufactured with Date Code 0627 (week 27, 2006) and newer are built with Green Molding Compound. Product manufactured prior to Date Code 0627 are built with Non-Green Molding Compound and may contain Halogens or Sb₂O₃ Fire Retardants.

Electrical Characteristics @ $T_A = 25^\circ\text{C}$ unless otherwise specified

Characteristic	Symbol	Min	Max	Unit	Test Condition
OFF CHARACTERISTICS (Note 5)					
Collector-Base Breakdown Voltage	$V_{(\text{BR})\text{CBO}}$	60	—	V	$I_C = 100\mu\text{A}, I_E = 0$
Collector-Emitter Breakdown Voltage	$V_{(\text{BR})\text{CEO}}$	40	—	V	$I_C = 1.0\text{mA}, I_B = 0$
Emitter-Base Breakdown Voltage	$V_{(\text{BR})\text{EBO}}$	6.0	—	V	$I_E = 100\mu\text{A}, I_C = 0$
Collector Cutoff Current	I_{CEX}	—	100	nA	$V_{\text{CE}} = 35\text{V}, V_{\text{EB}(\text{OFF})} = 0.4\text{V}$
Base Cutoff Current	I_{BL}	—	100	nA	$V_{\text{CE}} = 35\text{V}, V_{\text{EB}(\text{OFF})} = 0.4\text{V}$
ON CHARACTERISTICS (Note 5)					
DC Current Gain	h_{FE}	20	—	—	$I_C = 100\mu\text{A}, V_{\text{CE}} = 1.0\text{V}$
		40	—	—	$I_C = 1.0\text{mA}, V_{\text{CE}} = 1.0\text{V}$
		80	—	—	$I_C = 10\text{mA}, V_{\text{CE}} = 1.0\text{V}$
		100	300	—	$I_C = 150\text{mA}, V_{\text{CE}} = 1.0\text{V}$
		40	—	—	$I_C = 500\text{mA}, V_{\text{CE}} = 2.0\text{V}$
Collector-Emitter Saturation Voltage	$V_{\text{CE}(\text{SAT})}$	—	0.40 0.75	V	$I_C = 150\text{mA}, I_B = 15\text{mA}$ $I_C = 500\text{mA}, I_B = 50\text{mA}$
Base-Emitter Saturation Voltage	$V_{\text{BE}(\text{SAT})}$	0.75 —	0.95 1.2	V	$I_C = 150\text{mA}, I_B = 15\text{mA}$ $I_C = 500\text{mA}, I_B = 50\text{mA}$
SMALL SIGNAL CHARACTERISTICS					
Output Capacitance	C_{ob}	—	8.5	pF	$V_{\text{CB}} = 5.0\text{V}, f = 1.0\text{MHz}, I_E = 0$
Input Capacitance	C_{eb}	—	30	pF	$V_{\text{EB}} = 0.5\text{V}, f = 1.0\text{MHz}, I_C = 0$
Input Impedance	h_{ie}	1.0	15	k Ω	
Voltage Feedback Ratio	h_{re}	0.1	8.0	$\times 10^{-4}$	$V_{\text{CE}} = 10\text{V}, I_C = 1.0\text{mA}, f = 1.0\text{MHz}$
Small Signal Current Gain	h_{fe}	40	500	—	
Output Admittance	h_{oe}	1.0	30	μS	
Current Gain-Bandwidth Product	f_T	250	—	MHz	$V_{\text{CE}} = 10\text{V}, I_C = 20\text{mA}, f = 100\text{MHz}$
SWITCHING CHARACTERISTICS					
Delay Time	t_d	—	15	ns	$V_{\text{CC}} = 30\text{V}, I_C = 150\text{mA}, V_{\text{BE}(\text{OFF})} = 2.0\text{V}, I_{\text{B}1} = 15\text{mA}$
Rise Time	t_r	—	20	ns	
Storage Time	t_s	—	225	ns	$V_{\text{CC}} = 30\text{V}, I_C = 150\text{mA}, I_{\text{B}1} = I_{\text{B}2} = 15\text{mA}$
Fall Time	t_f	—	30	ns	

5. Short duration pulse test used to minimize self-heating effect.




Fig. 1, Max Power Dissipation vs Ambient Temperature









Fig. 2 Typical DC Current Gain vs Collector Current




Ordering Information (Note 4 & 6)

Device	Packaging	Shipping
MMST4401-7-F	SOT-323	3000/Tape & Reel

Notes: 6. For packaging details, go to our website at <http://www.diodes.com/datasheets/ap02007.pdf>.

Marking Information



K3X = Product Type Marking Code
 YM = Date Code Marking
 Y = Year ex: N = 2002
 M = Month ex: 9 = September

Date Code Key

Year	1998	1999	2000	2001	2002	2003	2004	2005	2006	2007	2008	2009	2010	2011	2012
Code	J	K	L	M	N	P	R	S	T	U	V	W	X	Y	Z

Month	Jan	Feb	Mar	Apr	May	Jun	Jul	Aug	Sep	Oct	Nov	Dec
Code	1	2	3	4	5	6	7	8	9	O	N	D

IMPORTANT NOTICE

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to any product herein. Diodes Incorporated does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on our website, harmless against all damages.

LIFE SUPPORT

Diodes Incorporated products are not authorized for use as critical components in life support devices or systems without the expressed written approval of the President of Diodes Incorporated.