



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DEDIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
UICFP2**	.54 LB/10 PCS (244.0 g/10 PCS)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
4. PART INCLUDES:
  - 1 - FACEPLATE
  - 1 - CLEAR SCREW COVER
  - 1 - COLOR COORDINATED SCREW COVER
  - 1 - CLEAR LABEL COVER
  - 2 - MOUNTING SCREW



MODEL FILENAME	SIZE
MO1279BA_UICFP2_03.PRT	A
DRAWING FILENAME	
MO1279BA_DC_03A.PRT	
MINI-COM™ ULTIMATE ID™ 2 POSITION VERTICAL CLASSIC SERIES FACEPLATE CUSTOMER DRAWING	
 <b>PANDUIT</b> ™ CORP. TINLEY PARK, ILL 60477	1.1. NUMBER N/A
	PRODUCT SPEC N/A
ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .010(.3) (.XX) ± .031(.8) ANGLES ±	WORK INSTRUCTION N/A
DRAWN BY JsP	SCALE NONE
REVIEW DRAWING NUMBERS	PART NO. UICFP2**
DATE 7-24-02	MATERIAL: ABS
CHK'D	DRAWING NO. 01279-06

REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP	OTH
R	7-24-02	JsP		RELEASED TO PRODUCTION	01279-06					

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[UICFP2WH](#)