

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [76060-0010](#)
Status: **Active**
Overview: [Impact™ Backplane Connectors and Cable Assemblies](#)
Description: Impact™ 100 Ohm 5 Pair Right Angle Daughtercard Receptacle, 1.90 by 1.35mm Pitch, Unguided, 10 Columns, 150 Circuits, Plated Through Hole Dimension 0.46mm, Tin (Sn), Lead (Pb)

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-76060-999 \(PDF\)](#)
[Application Specification AS-76060-990 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E29179

General

Product Family Backplane Connectors
Series [76060](#)
Application Coplanar, Daughtercard
Application Tooling Documents TM-622018799
Component Type PCB Receptacle
Overview [Impact™ Backplane Connectors and Cable Assemblies](#)
Product Name Impact™
Style N/A
UPC 883906421298

Physical

Circuits (Loaded) 150
Circuits (maximum) 150
Color - Resin Black
Durability (mating cycles max) 200
First Mate / Last Break No
Flammability 94V-0
Guide to Mating Part No
Keying to Mating Part None
Material - Metal High Performance Alloy (HPA)
Material - Plating Mating Gold
Material - Plating Termination Tin-Lead
Material - Resin High Temperature Thermoplastic
Number of Columns 10
Number of Pairs 5
Number of Rows 15
Orientation Right Angle
PC Tail Length 1.20mm
PCB Locator No
PCB Retention None
PCB Thickness - Recommended 1.00mm
Packaging Type Tray
Pitch - Mating Interface 1.90mm
Pitch - Termination Interface 1.90mm
Plating min - Mating 0.762µm
Polarized to PCB No
Stackable Yes
Temperature Range - Operating -55°C to +85°C
Termination Interface: Style Through Hole - Compliant Pin



image - Reference only

Series

EU RoHS
RoHS Compliant by Exemption
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[76060Series](#)

Mates With
[76055 Impact™ 100 Ohm Vertical Backplane Header](#)

Use With
[76153 Pirate Cannon Wide Guide Module](#)

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.
Global

Description	Product #
Impact Daughtercard Extraction Tool	0622024300

Electrical

Current - Maximum per Contact	0.75A
Data Rate	25.0 Gbps
Impedance	100#
Shield Type	N/A
Shielded	No
Voltage - Maximum	30V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Application Specification	AS-76060-990
Product Specification	PS-76060-999
Sales Drawing	SD-76060-001

This document was generated on 12/05/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[76060-0010](#)