






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		A	RELEASED	-	-	-



1546220-3 AS SHOWN

- ⚠ MATERIALS AND FINISH:
HOUSING: PA 6-6, UL 94-V0, COLOR GRAY.
CLAMP: BRASS, NICKEL PLATED.
TERMINAL: BRASS, TIN PLATED.
CLAMPING SCREW: M3, BRASS, NICKEL PLATED.
2. SUITABLE FOR 1,6-2,4mm PCB THICKNESS.
3. END-TO-END STACKABLE W/INTERLOCK, WITHOUT LOSS OF CENTERLINE SPACING.
4. WIRE RANGE: 12-30 AWG.
5. RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC. FILE N° E60677.
6. IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY WITH IEC 998-1/998-2-1.
- ⚠ NOT CUMULATIVE TOLERANCE.



RECOMMENDED PC BOARD LAYOUT

60	12	1-1546220-2
55	11	1-1546220-1
50	10	1-1546220-0
45	9	1546220-9
40	8	1546220-8
35	7	1546220-7
30	6	1546220-6
25	5	1546220-5
20	4	1546220-4
15	3	1546220-3
10	2	1546220-2
L	NO. OF POSN	PART NUMBER

DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN S. WELDON 02OCT2003	BUCHANAN Tyco Electronics Harrisburg, PA 17105-3608	
		9 PLC ± 2 PLC ±.3 3 PLC ±.25 4 PLC ± ANGLES ±2 FINISH		CHK C. RICHARD 02OCT2003		
				APVD C. RICHARD 02OCT2003	NAME TERMINAL BLOCK, PCB MOUNT ANGLED WIRE ENTRY, STACKING W/INTERLOCK, 5.08mm PITCH	
MATERIAL -				PRODUCT SPEC 108-20166		
				APPLICATION SPEC 114-20079	SIZE A 00779	
				WEIGHT -		
				CUSTOMER DRAWING	SCALE 3:1 SHEET 1 OF 1 REV A	