

PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION

**Part Number:** [15-91-0500](#)  
**Status:** **Active**  
**Overview:** [C-Grid® Products](#)  
**Description:** 2.54mm Pitch C-Grid® Header, Surface Mount, Dual Row, Vertical, 50 Circuits, 0.38µm Gold (Au) Selective Plating

**Documents:**  
[3D Model](#)  
[Drawing \(PDF\)](#)

[Product Specification PS-71308 \(PDF\)](#)  
[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR19980  
UL E29179

**General**

Product Family PCB Headers  
Series [71308](#)  
Application Board-to-Board, Signal, Wire-to-Board  
Overview [C-Grid® Products](#)  
Product Name C-Grid®  
UPC 800754395809

**Physical**

Breakaway Yes  
Circuits (Loaded) 50  
Circuits (maximum) 50  
Color - Resin Black  
Durability (mating cycles max) 50  
Flammability 94V-0  
Glow-Wire Compliant No  
Lock to Mating Part None  
Material - Metal Phosphor Bronze  
Material - Plating Mating Gold  
Material - Plating Termination Tin  
Material - Resin High Temperature Thermoplastic  
Net Weight 2.869/g  
Number of Rows 2  
Orientation Vertical  
PCB Locator No  
PCB Retention None  
Packaging Type Tube  
Pitch - Mating Interface 2.54mm  
Plating min - Mating 0.381µm  
Plating min - Termination 2.032µm  
Polarized to Mating Part No  
Polarized to PCB No  
Shrouded No  
Stackable Yes  
Temperature Range - Operating -40°C to +105°C  
Termination Interface: Style Surface Mount

**Electrical**

Current - Maximum per Contact 3A  
Voltage - Maximum 250V

**Solder Process Data**

Lead-free Process Capability Reflow Capable (SMT only)



Series

image - Reference only

**EU RoHS**

**ELV and RoHS  
Compliant**

**REACH SVHC**

Not Reviewed

**Low-Halogen Status**

**Not Reviewed**

**China RoHS**



**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
For a multiple part number RoHS Certificate of  
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any  
non-product compliance questions.

**Search Parts in this Series**  
[71308Series](#)

|                                    |                         |
|------------------------------------|-------------------------|
| Process Temperature max. C         | 260                     |
| <b>Material Info</b>               |                         |
| Old Part Number                    | 713080150N              |
| <b>Reference - Drawing Numbers</b> |                         |
| Product Specification              | PS-71308, RPS-71308-001 |
| Sales Drawing                      | SD-71308-001            |

This document was generated on 08/08/2014

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

15-91-0500