








THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO CW INDUSTRIES INCORPORATED AND ITS AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN CW INDUSTRIES PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM CW INDUSTRIES INCORPORATED, SOUTHAMPTON, PENNSYLVANIA USA.

Rating		21A 14VDC		Mounting Hole 		Circuit Diagram 	
Contact Resistance		50m ohm Max.					
Insulation Resistance		DC 500V 100M ohm Min.					
Dielectric Strength		AC 1500V 1 minute					
Operation Temperature		-25°~85°					
Switch Function		4P SPDT ON - OFF - ON Lamp Dependent		Thickness(mm)	X(mm)	Y(mm)	
Lamp Type		LED 12VDC 14V w/resistor		0.75~1.25	21.0 ^{+0.3} ₀	36.6+0.1	
				1.25~2.0		36.8+0.1	
				2.0~3.0		37.0+0.1	

Material:

1. Frame: Black, Nylon 66 (94V-2)
Actuator: Black, Nylon 66+33% GF
Lens 1: Red, PC
Lens 2: Green, PC
Terminal: Silver plated copper
(except lamp terminal)
Printed: None
2. Waterproof: IP-67



SEALANT ON BASE

TOLERANCE: ±0.3mm UNLESS OTHERWISE SPECIFIED.

RoHS Compliant

- | | |
|---|---|
| 3 | Added Dependent to Function & Lamp Type. 12/16/2011. |
| 2 | IP67 was I66 and added Sealant on base to bot. view. 8/24/10. |
| 1 | IP66 was IP67 & Removed Filled Epoxy from bot. view. 7/22/10 |

CW INDUSTRIES
Southampton, Pa. 18966
Tel 215.355.7080/www.cwind.com

Date Drawn: 9/29/09

Rev. 3

Unit: mm

Checked By: *G. Gold*

Title: **ROCKER SWITCH**

CW P/N: **GRB292D301BBRG1**