

## 3.2 Watt Plastic Surface Mount POWERMITE Package

### 1PMT5920B Series

This complete new line of 3.2 Watt Zener Diodes are offered in highly efficient micro miniature, space saving surface mount with its unique heat sink design. The POWERMITE package has the same thermal performance as the SMA while being 50% smaller in footprint area and delivering one of the lowest height profiles (1.1 mm) in the industry. Because of its small size, it is ideal for use in cellular phones, portable devices, business machines and many other industrial/consumer applications.

#### Features

- Zener Breakdown Voltage: 6.2 – 47 V
- DC Power Dissipation: 3.2 W with Tab 1 (Cathode) @ 75°C
- Low Leakage < 5  $\mu$ A
- ESD Rating of Class 3 (> 16 kV) per Human Body Model
- Low Profile – Maximum Height of 1.1 mm
- Integral Heat Sink/Locking Tabs
- Full Metallic Bottom Eliminates Flux Entrapment
- Small Footprint – Footprint Area of 8.45 mm<sup>2</sup>
- Supplied in 12 mm Tape and Reel
- Lead Orientation in Tape: Cathode (Short) Lead to Sprocket Holes
- POWERMITE is JEDEC Registered as DO-216AA
- Cathode Indicated by Polarity Band
- These Devices are Pb-Free and are RoHS Compliant

#### Mechanical Characteristics

**CASE:** Void-free, transfer-molded, thermosetting plastic



**FINISH:** All external surfaces are corrosion resistant and leads are readily solderable

**MOUNTING POSITION:** Any


**MAXIMUM CASE TEMPERATURE FOR SOLDERING PURPOSES:**

260°C for 10 Seconds

## PLASTIC SURFACE MOUNT 3.2 WATT ZENER DIODES 6.2 – 47 VOLTS



#### MARKING DIAGRAM



- M = Date Code
- xxB = Specific Device Code  
(See Table on Page 2)
- = Pb-Free Package

#### ORDERING INFORMATION

| Device       | Package                | Shipping <sup>†</sup> |
|--------------|------------------------|-----------------------|
| 1PMT59xxBT1G | POWERMITE<br>(Pb-Free) | 3000 / Tape &<br>Reel |

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

# 1PMT5920B Series

## MAXIMUM RATINGS


| Rating                                                                                      | Symbol                                 | Value       | Unit                                                    |
|---------------------------------------------------------------------------------------------|----------------------------------------|-------------|---------------------------------------------------------|
| DC Power Dissipation @ $T_A = 25^\circ\text{C}$ (Note 1)<br>Derate above $25^\circ\text{C}$ | $P_D$                                  | 500         | mW                                                      |
| Thermal Resistance, Junction-to-Ambient                                                     | $R_{\theta JA}$                        | 4.0<br>248  | $\text{mW}/^\circ\text{C}$<br>$^\circ\text{C}/\text{W}$ |
| Thermal Resistance, Junction-to-Lead (Anode)                                                | $R_{\theta JA\text{anode}}$            | 35          | $^\circ\text{C}/\text{W}$                               |
| Maximum DC Power Dissipation (Note 2)<br>Thermal Resistance from Junction-to-Tab (Cathode)  | $P_D$<br>$R_{\theta JC\text{cathode}}$ | 3.2<br>23   | W<br>$^\circ\text{C}/\text{W}$                          |
| Operating and Storage Temperature Range                                                     | $T_J, T_{\text{stg}}$                  | -55 to +150 | $^\circ\text{C}$                                        |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Mounted with recommended minimum pad size, PC board FR-4.
2. At Tab (Cathode) temperature,  $T_{\text{tab}} = 75^\circ\text{C}$

**ELECTRICAL CHARACTERISTICS** ( $T_L = 25^\circ\text{C}$  unless otherwise noted,  $V_F = 1.5\text{ V}$  Max. @  $I_F = 200\text{ mAdc}$  for all types)

| Symbol   | Parameter                          |
|----------|------------------------------------|
| $V_Z$    | Reverse Zener Voltage @ $I_{ZT}$   |
| $I_{ZT}$ | Reverse Current                    |
| $Z_{ZT}$ | Maximum Zener Impedance @ $I_{ZT}$ |
| $I_{ZK}$ | Reverse Current                    |
| $Z_{ZK}$ | Maximum Zener Impedance @ $I_{ZK}$ |
| $I_R$    | Reverse Leakage Current @ $V_R$    |
| $V_R$    | Reverse Voltage                    |
| $I_F$    | Forward Current                    |
| $V_F$    | Forward Voltage @ $I_F$            |



**ELECTRICAL CHARACTERISTICS** ( $T_L = 30^\circ\text{C}$  unless otherwise noted,  $V_F = 1.25\text{ Volts}$  @  $200\text{ mA}$ )

| Device*      | Device Marking | Zener Voltage (Note 3)                   |     |       | I <sub>ZT</sub> | I <sub>R</sub> @ V <sub>R</sub> | V <sub>R</sub> | Z <sub>ZT</sub> @ I <sub>ZT</sub><br>(Note 4) | Z <sub>ZK</sub> @ I <sub>ZK</sub><br>(Note 4) | I <sub>ZK</sub> |
|--------------|----------------|------------------------------------------|-----|-------|-----------------|---------------------------------|----------------|-----------------------------------------------|-----------------------------------------------|-----------------|
|              |                | V <sub>Z</sub> @ I <sub>ZT</sub> (Volts) |     |       |                 |                                 |                |                                               |                                               |                 |
|              |                | Min                                      | Nom | Max   | (mA)            | (μA)                            | (V)            | (Ω)                                           | (Ω)                                           | (mA)            |
| 1PMT5920BT1G | 20B            | 5.89                                     | 6.2 | 6.51  | 60.5            | 5.0                             | 4.0            | 2.0                                           | 200                                           | 1.0             |
| 1PMT5921BT1G | 21B            | 6.46                                     | 6.8 | 7.14  | 55.1            | 5.0                             | 5.2            | 2.5                                           | 200                                           | 1.0             |
| 1PMT5924BT1G | 24B            | 8.64                                     | 9.1 | 9.56  | 41.2            | 5.0                             | 7.0            | 4.0                                           | 500                                           | 0.5             |
| 1PMT5927BT1G | 27B            | 11.4                                     | 12  | 12.6  | 31.2            | 1.0                             | 9.1            | 6.5                                           | 550                                           | 0.25            |
| 1PMT5929BT1G | 29B            | 14.25                                    | 15  | 15.75 | 25              | 1.0                             | 11.4           | 9.0                                           | 600                                           | 0.25            |
| 1PMT5933BT1G | 33B            | 20.9                                     | 22  | 23.1  | 17              | 1.0                             | 16.7           | 17.5                                          | 650                                           | 0.25            |
| 1PMT5934BT1G | 34B            | 22.8                                     | 24  | 25.2  | 15.6            | 1.0                             | 18.2           | 19                                            | 700                                           | 0.25            |
| 1PMT5935BT1G | 35B            | 25.65                                    | 27  | 28.35 | 13.9            | 1.0                             | 20.6           | 23                                            | 700                                           | 0.25            |
| 1PMT5941BT1G | 41B            | 44.65                                    | 47  | 49.35 | 8.0             | 1.0                             | 35.8           | 67                                            | 1000                                          | 0.25            |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

3. Zener voltage is measured with the device junction in thermal equilibrium with an ambient temperature of  $25^\circ\text{C}$ .
4. Zener Impedance Derivation  $Z_{ZT}$  and  $Z_{ZK}$  are measured by dividing the AC voltage drop across the device by the AC current applied. The specified limits are for  $I_Z(\text{ac}) = 0.1 I_Z(\text{dc})$  with the ac frequency =  $60\text{ Hz}$ .

# 1PMT5920B Series

## TYPICAL CHARACTERISTICS




Figure 1. Steady State Power Derating




Figure 2.  $V_Z$  to 10 Volts




Figure 3.  $V_Z = 12$  thru 47 Volts




Figure 4. Zener Voltage - To 12 Volts




Figure 5. Zener Voltage - 14 To 47 Volts




Figure 6. Effect of Zener Voltage

# 1PMT5920B Series

## TYPICAL CHARACTERISTICS




Figure 7. Effect of Zener Current





Figure 8. Capacitance versus Reverse Zener Voltage



**POWERMITE 1.90x1.96x1.00**  
**CASE 457**  
**ISSUE H**


DATE 16 MAY 2025



| MILLIMETERS |          |      |      |
|-------------|----------|------|------|
| DIM         | MIN      | NOM  | MAX  |
| A           | 0.85     | 1.00 | 1.15 |
| A1          | 0.00     | 0.05 | 0.10 |
| b           | 0.40     | 0.55 | 0.69 |
| b1          | 0.70     | 0.85 | 1.00 |
| c           | 0.10     | 0.18 | 0.25 |
| D           | 1.75     | 1.90 | 2.05 |
| E           | 1.75     | 1.96 | 2.18 |
| H           | 3.60     | 3.75 | 3.90 |
| L           | 1.20     | 1.35 | 1.50 |
| L1          | 0.50     | 0.65 | 0.80 |
| L2          | 0.50 REF |      |      |

- NOTES:
1. DIMENSIONING AND TOLERANCING AS PER ASME Y14.5M, 2018.
  2. CONTROLLING DIMENSION: MILLIMETERS.
  3. DIMENSION D & E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS OR GATE BURRS.

**GENERIC MARKING DIAGRAMS\***



STYLE 1:  
PIN 1: CATHODE  
2: ANODE

STYLE 2:  
PIN 1: ANODE OR CATHODE  
2: CATHODE OR ANODE (BI-DIRECTIONAL)

STYLE 3:  
PIN 1: ANODE  
2: CATHODE

XXX = Specific Device Code  
M = Date Code  
▪ = Pb-Free Package

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "▪", may or may not be present. Some products may not follow the Generic Marking.

|                         |                                 |                                                                                                                                                                                  |
|-------------------------|---------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>DOCUMENT NUMBER:</b> | <b>98ASB14853C</b>              | Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| <b>DESCRIPTION:</b>     | <b>POWERMITE 1.90x1.96x1.00</b> | <b>PAGE 1 OF 1</b>                                                                                                                                                               |

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at  
[www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)