


Inductors, Commercial, Miniature, Molded, Shielded, Axial Leaded



ELECTRICAL SPECIFICATIONS

Inductance Range: 0.1 μ H to 820 μ H

Inductance Tolerance: $\pm 10\%$

Dielectric Strength: 700 V_{RMS} at sea level

Operating Temperature: - 55 °C to + 125 °C

Self-Resonant Frequency: Measured per MIL-PRF-15305 (latest revision)

Q: Measured on a Q-meter

Maximum Current: Based on temperature rise not to exceed 35 °C at + 90 °C ambient

MECHANICAL SPECIFICATIONS

Terminal Strength: Meets 5 lb pull test, three 360° rotations in alternate directions when tested per MIL-PRF-15305 (latest revision)

FEATURES

- Ultra-reliable molded shielded miniature RF inductor
- Epoxy molded envelope and shielding
- Offers reliability, electrical performance and minimum coupling in high density packaging
- Compliant to RoHS directive 2002/95/EC



RoHS
COMPLIANT

DENSITY SPECIFICATIONS

Weight: 0.75 g maximum

Shielding: At the test frequency, two units assembled side by side exhibit less than 3 % coupling


ENVIRONMENTAL SPECIFICATIONS

Moisture: Per MIL-STD-202, method 106

Vibration: High frequency, 10 Hz to 2000 Hz at 20 G $\pm 10\%$ maximum for 12 logarithmic swings each of 20 min duration repeated for each of three mutually perpendicular planes

Shock: 100 g, 6 ms

DIMENSIONS in inches [millimeters]



STANDARD ELECTRICAL SPECIFICATIONS

MODEL	IND. (μ H)	TOL. (%)	Q MIN.	TEST FREQUENCY Q (MHz)	SRF MIN. (MHz)	DCR MAX. (Ω)	RATED DC CURRENT (mA)	INCREMENTAL CURRENT (mA) ⁽¹⁾	PHENOLIC CORE
IMS-5SWD-65	0.10	± 10	50	25	250	0.025	2900	2900	
IMS-5SWD-65	0.12	± 10	51	25	250	0.034	2800	2800	
IMS-5SWD-65	0.15	± 10	51	25	250	0.037	2750	2750	
IMS-5SWD-65	0.18	± 10	50	25	250	0.047	2200	2200	
IMS-5SWD-65	0.22	± 10	49	25	250	0.067	1700	1700	
IMS-5SWD-65	0.27	± 10	47	25	250	0.11	1500	1500	
IMS-5SWD-65	0.33	± 10	46	25	250	0.13	1300	1300	
IMS-5SWD-65	0.39	± 10	44	25	250	0.18	1100	1100	
IMS-5SWD-65	0.47	± 10	44	25	235	0.25	1000	1000	
IMS-5SWD-65	0.56	± 10	43	25	210	0.33	900	900	
IMS-5SWD-65	0.68	± 10	42	25	190	0.45	750	750	
IMS-5SWD-65	0.82	± 10	40	25	180	0.59	600	600	

Note

⁽¹⁾ Incremental Current: The DC current required to cause a 5 % reduction in the nominal inductance value

STANDARD ELECTRICAL SPECIFICATIONS

MODEL	IND. (μ H)	TOL. (%)	Q MIN.	TEST FREQUENCY Q (MHz)	SRF MIN. (MHz)	DCR MAX. (Ω)	RATED DC CURRENT (mA)	INCREMENTAL CURRENT (mA) ⁽¹⁾	
IMS-5SWD-65	1.0	± 10	47	25	140	0.07	1900	1900	IRON CORE
IMS-5SWD-65	1.2	± 10	46	7.9	130	0.093	1600	1600	
IMS-5SWD-65	1.5	± 10	45	7.9	115	0.12	1300	1300	
IMS-5SWD-65	1.8	± 10	43	7.9	105	0.14	1200	1200	
IMS-5SWD-65	2.2	± 10	45	7.9	100	0.19	1100	1100	
IMS-5SWD-65	2.7	± 10	46	7.9	92	0.28	950	950	
IMS-5SWD-65	3.3	± 10	44	7.9	85	0.35	800	800	
IMS-5SWD-65	3.9	± 10	44	7.9	75	0.40	750	750	
IMS-5SWD-65	4.7	± 10	44	7.9	70	0.55	650	650	
IMS-5SWD-65	5.6	± 10	47	7.9	65	0.72	550	550	
IMS-5SWD-65	6.8	± 10	50	7.9	55	1.02	500	500	
IMS-5SWD-65	8.2	± 10	50	7.9	50	1.32	475	475	
IMS-5SWD-65	10	± 10	49	7.9	46	1.62	450	450	
IMS-5SWD-65	12	± 10	55	2.5	44	2.0	400	400	
IMS-5SWD-65	15	± 10	44	2.5	49	0.80	620	250	FERRITE CORE
IMS-5SWD-65	18	± 10	45	2.5	45	0.89	610	235	
IMS-5SWD-65	22	± 10	46	2.5	41	0.96	600	220	
IMS-5SWD-65	27	± 10	49	2.5	38	1.19	500	200	
IMS-5SWD-65	33	± 10	45	2.5	34	1.37	490	190	
IMS-5SWD-65	39	± 10	53	2.5	29	1.93	410	180	
IMS-5SWD-65	47	± 10	52	2.5	27	2.11	400	175	
IMS-5SWD-65	56	± 10	49	2.5	25	2.23	380	160	
IMS-5SWD-65	68	± 10	51	2.5	21	2.70	370	150	
IMS-5SWD-65	82	± 10	45	2.5	10.5	2.44	360	140	
IMS-5SWD-65	100	± 10	52	2.5	10	3.12	325	120	
IMS-5SWD-65	120	± 10	57	0.79	9.7	3.6	290	95	
IMS-5SWD-65	150	± 10	56	0.79	8.5	4.1	275	90	
IMS-5SWD-65	180	± 10	60	0.79	8.0	4.4	260	85	
IMS-5SWD-65	220	± 10	58	0.79	7.5	5.0	250	80	
IMS-5SWD-65	270	± 10	60	0.79	7.0	5.8	240	70	
IMS-5SWD-65	330	± 10	54	0.79	6.5	6.4	225	65	
IMS-5SWD-65	390	± 10	67	0.79	6.2	7.4	200	60	
IMS-5SWD-65	470	± 10	60	0.79	5.7	9.5	180	58	
IMS-5SWD-65	560	± 10	60	0.79	4.7	10.5	174	55	
IMS-5SWD-65	680	± 10	60	0.79	4.5	11.8	168	50	
IMS-5SWD-65	820	± 10	57	0.79	4.2	13.0	152	45	

Note

⁽¹⁾ Incremental Current: The DC current required to cause a 5 % reduction in the nominal inductance value

MARKING

- Color coded per MIL-PRF-15305

ORDERING INFORMATION

IMS-5SWD-65 MODEL	0.47 μ H INDUCTANCE VALUE	10 % INDUCTANCE TOLERANCE	ER PACKAGE CODE	e2 JEDEC LEAD (Pb)-FREE STANDARD
----------------------	-------------------------------------	---------------------------------	-----------------------	--

GLOBAL PART NUMBER

GLOBAL PART NUMBER														
I	M	S	5	S	W	D	E	R	R	4	7	K	6	5
MODEL							PACKAGE CODE		INDUCTANCE VALUE			INDUCTANCE TOLERANCE	SERIES	



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.