

Product SKU:	C1320.21.03
Product Description:	Hook-Up Wire, PVC Test Lead, No. of Conductors: 1, Gauge Size (AWG): 18, Conductor/Strands: 65/36, Temperature Range: -25Â°C to +60Â°C - Red - 1000 Ft. Spool
Product Category:	Electronics - Hook-Up Wire - Rubber/PVC Test Lead - PVC Test Lead - Red

**Product Construction:**

Conductor:	Fully-annealed, stranded tinned copper per ASTM B-33
Insulation:	- Temperature range: -25Â°C to +60Â°C PVC - Premium grade color coded Polyvinylchloride (PVC)

Product Specification:

No. of Conductors:	1
Conductor Size (AWG):	18
Conductor/Strands:	65/36
Jacket Color:	Red
Nominal Insulation Thickness (in):	0.045
Nominal Insulation Thickness (mm):	1.14
Breakdown Voltage (AC,ms):	20,000V
Working Voltage:	5,000V
Nominal Outside Diameter (in):	0.140
Nominal Outside Diameter (mm):	3.56
Standard Packaging:	1000' Spool

Standard Package Quantity:	1
UPC #:	079407815135
Footnote:	For intermittent duty only.
Put-up:	1000
SCC-14:	50079407815133
Cube:	528.471
Weight Per Unit of Measure:	.01
ColorOption:	Red

Product Information:

Applications:	- Oscillators - Test equipment
Packaging:	1000' (305 m) Spools 500' (152m) Reels 5000' (1524m) Reels - Other put-ups available- consult Customer Service

Reference Charts

[Color Code Chart](#)

Technical Specifications

[Unit Conversion Factors](#)

[Cable Design Equations - Balanced Pair](#)

[Insulation and Jacket Properties](#)

[Temperature Conversion Chart](#)

[Decimal and Unit Conversion Factors](#)

[Cable Design Equations - Braid Shield](#)

[AWG Conductor Chart](#)

[Conduit Capacity Chart](#)

[Cable Design Equations - Coaxial Cable](#)

[Engineering Prefixes](#)

[Coax Connector Cross Reference](#)

[Glossary](#)

**CAROL
BRAND**