





PIN RECEPTACLES
 for .015" - .018" diameter pins (#09 contact)
 for .015" - .020" diameter pins (#11 contact)
 and .015" - .022" diameter pins (#21 contact)
 (see specific contact range on pages 216 & 217)


**0467**

0467-0-15-XX-21-XX-04-0
 Press-fit in .037 mounting hole


0552

0552-X-15-XX-X1-XX-10-0
 Solder mount in .040 min. mounting hole
 Also available on 16mm wide carrier
 tape: 1,500 parts per 13" reel.
 Order as: 0552-X-57-XX-X1-XX-10-0


Basic Part Number	Length L	Depth N
0552-1	.136	.120
0552-2	.170	.150

5522


5522-0-15-XX-09-XX-10-0
 Solder mount in .040 min. mounting hole

0569


0569-0-15-XX-X1-XX-10-0
 Solder mount in .040 min mounting hole

6023


6023-0-15-XX-21-XX-10-0
 Solder mount in .040 min mounting hole

6214

6214-0-15-XX-21-XX-10-0
 Solder mount in .040 min mounting hole


2086

2086-0-15-XX-21-XX-04-0
 Press-fit in .040 mounting hole

0461

0461-X-15-XX-X1-XX-04-0
 Solder mount in .020 min. mounting hole

Basic Part Number	Length A
0461-0	.400
0461-1	.275
0461-2	.180
0461-3	.125
0461-4	.060
0461-5	.440

8579

8579-0-15-XX-X1-XX-10-0
 Solder mount in .040 min mounting hole

Basic Part Number	Length L
8579-0	.234
8579-1	.295

SPECIFICATIONS

SHELL MATERIAL:
 Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
 Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES
TOLERANCES ON:
 LENGTHS: ±.005
 DIAMETERS: ±.002
 ANGLES: ± 2°

ORDER CODE: XXXX - X - 15 - XX - XX - XX - XX - 0

BASIC PART # →
SPECIFY SHELL FINISH:
 01 200μ" TIN/LEAD OVER NICKEL
 80 200μ" TIN OVER NICKEL ◇
 15 10μ" GOLD OVER NICKEL ◇

SPECIFY CONTACT FINISH:
 02 100μ" TIN/LEAD OVER NICKEL
 84 100μ" TIN OVER NICKEL ◇
 27 30μ" GOLD OVER NICKEL ◇



SELECT CONTACT
 #09, #11 or #21 CONTACT (DATA ON PAGE 217)