

LOC	DIST	REVISIONS						
		P	LTR	DESCRIPTION	DATE	DWN	APVD	
		A4		ECR-12-006809	23APR2013	MT	YHM	
		A5		ECR-14-003140	17Mar2014	WRP	YHM	
		A6		ECR-14-004083	21Mar2014	WW	RR	
		A7		ECR-15-002179	20JAN2015	Rayb	Ric	

NOTE
1 HOUSING HAS RAST 5 COMPLIANT KEYING, LATCHING, AND POLARIZATION
TAB IS 6.30 X 0.8 ACCORDING TO DIN 46244

2 SEE SHEET 2 FOR AVAILABLE CONFIGURATIONS

3 MATERIAL: HOUSING, NYLON, UL94 V0, 750°C GWT NO FLAME
CONTACT, COPPER ALLOY, 0.8MM THICK

4 FINISH: CONTACTS, MATT TIN PLATING OVERALL, NICKEL UNDER-PLATING
BRIGHT TIN PLATING OVERALL, NICKEL UNDER-PLATING
SILVER PLATING OVERALL, NICKEL UNDER-PLATING







5 PCB TABS INSERTED IN A STAGGERED PATTERN BEGINNING WITH
POSITION 1 (C<+1)

6 THE PART NUMBERS SHOWING IN SHEET 2 & 3 & 4 & 5
ARE FOR NATURAL COLOR . THE PART NUMBER FOR OTHER COLOR
ARE BASED ON THE NATURAL ONE: FOR THE SAME CONFIGURATION,
THE PREFIX AND POSTFIX OF THE P/N ARE THE SAME, ONLY THE
BASE NUMBER IS DIFFERENT ACCORDING TO DIFFERENT COLOR,
DETAIL PLEASE SEE SHEET 6


7 PACKAGING: LOOSE PIECE OR TUBE. THE PART NUMBERS IN THIS
DRAWING ARE WITH LOOSE PIECE PACKAGING. PLEASE CONTACT TE
SALES REPRESENTATIVES FOR TUBE PACKAGING REQUIREMENT.

8 PRELIMINARY PART NOT RELEASED FOR PRODUCTION


9 FOR P/N: 8-2232043-7:
1) THE CONTACTS ARE WITH BRIGHT TIN PLATING ACCORDING TO
STANDARD:ASTM B 545.



SECTION A-A



RECOMMEND PCB LAYOUT - SOLDER SIDE
EVEN NUMBER OF PINS
PCB 15±0.2 THICK



RECOMMEND PCB LAYOUT - SOLDER SIDE
ODD NUMBER OF PINS
PCB 15±0.2 THICK

42.30	40.30	8
37.30	35.30	7
32.30	30.30	6
27.30	25.30	5
22.30	20.30	4
17.30	15.30	3
12.30	10.30	2
N	M	NO. OF POS.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Raybin.Wu 17Mar2014	NAME RAST 5 TAB HEADER ASSY, OPPOSITE DIN STYLE, TH, VERTICAL	
DIMENSIONS: mm		CHK Jain.Liu 17Mar2014		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD Robone_Rickard 17Mar2014	PRODUCT SPEC 108-106080	
0 PLC ±		APPLICATION SPEC		SIZE CAGE CODE DRAWING NO
1 PLC ±		WEIGHT		RESTRICTED TO
2 PLC ±		Customer Drawing		SCALE N/A SHEET 1 OF 6 REV A7
3 PLC ±				
4 PLC ±				
ANGLES				
FINISH				

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	OWN	APVD
ES	00		-	SEE SHEET 1	-	-	-

8	TAB CONTACT MATT TIN PLATING (8-2232043-7 IS WITH BRIGHT TIN)	1	RAST 5 TAB HEADER HOUSING,8P,NATURE (SEE THE DETAIL LAYOUT ON SHEET 5)	8	5-2232043-8		
7		1	RAST 5 TAB HEADER HOUSING,7P,NATURE (SEE THE DETAIL LAYOUT ON SHEET 5)	7	4-2232043-8		
					3-2232043-8		
					2-2232043-8		
					1-2232043-8		
					2232043-8		
					9-2232043-7		
					8-2232043-7 		
					7-2232043-7		
					6-2232043-7		
					5-2232043-7		
6		1	RAST 5 TAB HEADER HOUSING,6P,NATURE (SEE THE DETAIL LAYOUT ON SHEET 5)	6	4-2232043-7		
					3-2232043-7		
					2-2232043-7		
					1-2232043-7		
					2232043-7		
					2232045-6		
					9-2232043-6		
					8-2232043-6		
					7-2232043-6		
					6-2232043-6		
5		1	RAST 5 TAB HEADER HOUSING,5P,NATURE (SEE THE DETAIL LAYOUT ON SHEET 4)	5	5-2232043-6		
					4-2232043-6		
					3-2232043-6		
					2-2232043-6		
					1-2232043-6		
					2232043-6		
					2232512-5		
	9-2232043-5						
	8-2232043-5						
	7-2232043-5						
QTY		②	QTY		①	NO. OF POS.	TE PART NO.

4	TAB CONTACT MATT TIN PLATING	1	RAST 5 TAB HEADER HOUSING,4P,NATURE (SEE THE DETAIL LAYOUT ON SHEET 4)	4	5-2232045-4
					4-2232045-4
					3-2232045-4
					2-2232045-4
					1-2232045-4
					2232045-4
					9-2232043-4
					8-2232043-4
					7-2232043-4
					6-2232043-4
					5-2232043-4
					4-2232043-4
					3-2232043-4
					2-2232043-4
					1-2232043-4
2232043-4					
3	TAB CONTACT MATT TIN PLATING	1	RAST 5 TAB HEADER HOUSING,3P,NATURE (SEE THE DETAIL LAYOUT ON SHEET 4)	3	 4-2232045-3
					 3-2232045-3
					2-2232045-3
					1-2232045-3
					2232045-3
					9-2232043-3
					8-2232043-3
					7-2232043-3
					6-2232043-3
					5-2232043-3
					4-2232043-3
					3-2232043-3
					2-2232043-3
					1-2232043-3
					2232043-3
2	TAB CONTACT MATT TIN PLATING	1	RAST 5 TAB HEADER HOUSING,2P,NATURE (SEE THE DETAIL LAYOUT ON SHEET 4)	2	4-2232045-2
					3-2232045-2
					2-2232045-2
					1-2232045-2
					2232045-2
					9-2232043-2
					8-2232043-2
					7-2232043-2
					6-2232043-2
					5-2232043-2
					4-2232043-2
					3-2232043-2
					2-2232043-2
					1-2232043-2
					2232043-2
QTY	②	QTY	①	NO. OF POS.	TE PART NO.


THIS DRAWING IS A CONTROLLED DOCUMENT.

OWN
RUIPING WU
30-Jan-13

CHK
HAPYE WU
30-Jan-13

APVD
YHM
30-Jan-13

DIMENSIONS:
mm



0 PLC ±
1 PLC ±
2 PLC ±0.25
3 PLC ±
4 PLC ±
ANGLES ±2°
FINISH

MATERIAL
-

FINISH
-

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

NAME
RAST 5 TAB HEADER ASSY, OPPOSITE
DIN STYLE, TH, VERTICAL

SIZE
A1

CAGE CODE
00779

DRAWING NO.
2232043

RESTRICTED TO
-

SCALE
N/A

SHEET
2

OF
6

REV
A6

4805 (3/11)


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
ES	00		-	SEE SHEET 1	-	-	-

8	TAB CONTACT w/ SILVER PLATING	1	RAST 5 TAB HEADER HOUSING,8P,NATURE (SEE THE DETAIL LAYOUT ON SHEET 5)	8	5-2232044-8	
7		1	RAST 5 TAB HEADER HOUSING,7P,NATURE (SEE THE DETAIL LAYOUT ON SHEET 5)	7	4-2232044-8	
					3-2232044-8	
					2-2232044-8	
					1-2232044-8	
					2232044-8	
					9-2232044-7	
					8-2232044-7	
					7-2232044-7	
6		1	RAST 5 TAB HEADER HOUSING,6P,NATURE (SEE THE DETAIL LAYOUT ON SHEET 5)	6	6-2232044-7	
					5-2232044-7	
					4-2232044-7	
					3-2232044-7	
					2-2232044-7	
					1-2232044-7	
					2232044-7	
					2232046-6	
5		1	RAST 5 TAB HEADER HOUSING,5P,NATURE (SEE THE DETAIL LAYOUT ON SHEET 4)	5	9-2232044-6	
					8-2232044-6	
					7-2232044-6	
					6-2232044-6	
					5-2232044-6	
					4-2232044-6	
					3-2232044-6	
					2-2232044-6	
QTY		②	QTY	①	NO. OF POS.	1-2232044-6
						2232044-6
						9-2232044-5
						8-2232044-5
						7-2232044-5
						6-2232044-5
						5-2232044-5
	4-2232044-5					
TE PART NO.					3-2232044-5	
					2-2232044-5	
					1-2232044-5	
					2232044-5	

4	TAB CONTACT w/ SILVER PLATING	1	RAST 5 TAB HEADER HOUSING,4P,NATURE (SEE THE DETAIL LAYOUT ON SHEET 4)	4		5-2232046-4
					4-2232046-4	
					3-2232046-4	
					2-2232046-4	
					1-2232046-4	
					2232046-4	
					9-2232044-4	
					8-2232044-4	
					7-2232044-4	
					6-2232044-4	
					5-2232044-4	
					4-2232044-4	
					3-2232044-4	
					2-2232044-4	
					1-2232044-4	
					2232044-4	
3		1	RAST 5 TAB HEADER HOUSING,3P,NATURE (SEE THE DETAIL LAYOUT ON SHEET 4)	3	△8	4-2232046-3
					△8	3-2232046-3
					2-2232046-3	
					1-2232046-3	
					2232046-3	
					9-2232044-3	
					8-2232044-3	
					7-2232044-3	
2	1	RAST 5 TAB HEADER HOUSING,2P,NATURE (SEE THE DETAIL LAYOUT ON SHEET 4)	2		6-2232044-3	
				5-2232044-3		
				4-2232044-3		
				3-2232044-3		
				2-2232044-3		
				1-2232044-3		
				2232044-3		
				4-2232046-2		
3-2232046-2						
2-2232046-2						
1-2232046-2						
2232046-2						
9-2232044-2						
8-2232044-2						
7-2232044-2						
6-2232044-2						
5-2232044-2						
4-2232044-2						
3-2232044-2						
2-2232044-2						
1-2232044-2						
2232044-2						
QTY	②	QTY	①	NO. OF POS.	TE PART NO.	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±
2 PLC ±0.25
3 PLC ±
4 PLC ±
ANGLES ±2°
FINISH -

DWN
RUIPING_WU
30-Jan-13

CHK
HAPYE_WU
30-Jan-13

APVD
YHM
30-Jan-13

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

NAME
RAST 5 TAB HEADER ASSY. OPPOSITE
DIN STYLE, TH, VERTICAL
-

SIZE
A1

CAGE CODE
00779

DRAWING NO.
2232043

RESTRICTED TO
-


SCALE
N/A

SHEET
3


OF
6

REV
A6


LOC	DIST	REVISIONS					
ES	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		-	-	SEE SHEET 1	-	-	-




2232043-2
2232044-2




2232045-2
2232046-2




2232043-3
2232044-3




2232045-3
2232046-3




2232043-4
2232044-4




2232045-4
2232046-4




2232043-5
2232044-5




2232512-5




1-2232043-2
1-2232044-2




1-2232045-2
1-2232046-2




1-2232043-3
1-2232044-3




1-2232045-3
1-2232046-3




1-2232043-4
1-2232044-4




1-2232045-4
1-2232046-4




1-2232043-5
1-2232044-5




2-2232043-2
2-2232044-2




2-2232045-2
2-2232046-2




2-2232043-3
2-2232044-3




2-2232045-3
2-2232046-3




2-2232043-4
2-2232044-4




2-2232045-4
2-2232046-4




2-2232043-5
2-2232044-5




3-2232043-2
3-2232044-2




3-2232045-2
3-2232046-2




3-2232043-3
3-2232044-3




3-2232045-3 $\triangle/8$
3-2232046-3 $\triangle/8$




3-2232043-4
3-2232044-4




3-2232045-4
3-2232046-4




3-2232043-5
3-2232044-5




4-2232043-2
4-2232044-2




4-2232045-2
4-2232046-2




4-2232043-3
4-2232044-3




4-2232045-3 $\triangle/8$
4-2232046-3 $\triangle/8$




4-2232043-4
4-2232044-4




4-2232045-4
4-2232046-4




4-2232043-5
4-2232044-5




5-2232043-2
5-2232044-2




5-2232043-3
5-2232044-3




5-2232043-4
5-2232044-4




5-2232045-4
5-2232046-4




5-2232043-5
5-2232044-5




6-2232043-2
6-2232044-2




6-2232043-3
6-2232044-3




6-2232043-4
6-2232044-4




6-2232043-5
6-2232044-5




7-2232043-2
7-2232044-2




7-2232043-3
7-2232044-3




7-2232043-4
7-2232044-4




7-2232043-5
7-2232044-5




8-2232043-2
8-2232044-2




8-2232043-3
8-2232044-3




8-2232043-4
8-2232044-4




8-2232043-5
8-2232044-5




9-2232043-2
9-2232044-2




9-2232043-3
9-2232044-3




9-2232043-4
9-2232044-4




9-2232043-5
9-2232044-5




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RUIPING.WU 30-Jan-13	 TE Connectivity										
DIMENSIONS:		CHK HAPYE.WU 30-Jan-13											
mm		APVD YHM 30-Jan-13	NAME		RAST 5 TAB HEADER ASSY, OPPOSITE DIN STYLE, TH, VERTICAL								
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC									
		0 PLC ± 1 PLC ±0.25 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH		APPLICATION SPEC									
MATERIAL		WEIGHT		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO					
-		-		A1		100779	C=2232043	-					
CUSTOMER DRAWING				SCALE		N/A		SHEET	4	OF	6	REV	A6


LOC	DIST	REVISIONS					
ES	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		-	-	SEE SHEET 1	-	-	-




2232043-6
2232044-6




2232045-6
2232046-6




2232043-7
2232044-7




2232043-8
2232044-8




1-2232043-6
1-2232044-6




1-2232043-7
1-2232044-7




1-2232043-8
1-2232044-8




2-2232043-6
2-2232044-6




2-2232043-7
2-2232044-7




2-2232043-8
2-2232044-8




3-2232043-6
3-2232044-6




3-2232043-7
3-2232044-7




3-2232043-8
3-2232044-8




4-2232043-6
4-2232044-6




4-2232043-7
4-2232044-7




4-2232043-8
4-2232044-8




5-2232043-6
5-2232044-6




5-2232043-7
5-2232044-7




5-2232043-8
5-2232044-8




6-2232043-6
6-2232044-6




6-2232043-7
6-2232044-7




7-2232043-6
7-2232044-6




7-2232043-7
7-2232044-7




8-2232043-6
8-2232044-6




8-2232043-7
8-2232044-7



9-2232043-6
9-2232044-6




9-2232043-7
9-2232044-7



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RUIPING WU 30-Jan-13	TE TE Connectivity NAME RAST 5 TAB HEADER ASSY, OPPOSITE DIN STYLE, TH, VERTICAL				
DIMENSIONS:		CHK HAPYE WU 30-Jan-13					
mm		APVD YHM 30-Jan-13	PRODUCT SPEC -		SIZE A1		
		APPLICATION SPEC -		CAGE CODE 00779		DRAWING NO 2232043	
MATERIAL -		WEIGHT -		CUSTOMER DRAWING		RESTRICTED TO -	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		SCALE N/A		SHEET 5 OF 6		REV A6	
0 PLC ± 1 PLC ± 2 PLC ±0.25 3 PLC ± 4 PLC ± ANGLES ±2° FINISH							

LOC		DIST		REVISIONS					
-		-		P	LTR	DESCRIPTION	DATE	DWN	APVD


FOR ANY KEYING CONFIGURATION, THERE ARE EIGHT COLORS AVAILABLE. BESIDES THE NATURAL COLOR, THERE ARE OTHER SEVEN COLORS, INCLUDE: YELLOW, BLUE, GREY, PURPLE, RED, GREEN, BLACK. THE WHITE VERSION IS PRELIMINARY. THE P/N OF THE COLOR CONNECTOR ARE BASED ON THE NATURAL CONNECTOR, THE PREFIX AND POSTFIX ARE THE SAME FOR THE SAME KEYING CONFIGURATION, BUT THE BASE NUMBERS ARE DIFFERENT ACCORDING TO DIFFERENT COLOR. THE FOLLOWING SHOWS WHAT'S THE P/N FOR COLOR CONNECTOR



COLOR	PART NUMBER OF THE CONNECTOR				COMMENTS
	WITH MATT TIN PLATING CONTACT (SPECIAL P/N: 8-2232043-7 ARE WITH BRIGHT TIN)		 WITH AG PLATING CONTACT		
NATURAL	#-2232043-# 	#-2232045-#	#-2232044-#	#-2232046-#	THE PREFIX AND POSTFIX ARE THE SAME WITH THE P/N OF THE NATURAL CONNECTOR FOR THE SAME KEYING CONFIGURATION, JUST THE BASE NUMBERS ARE DIFFERENT BASED ON DIFFERENT COLOR. # CAN BE THE NUMBER FROM 0 TO 9.
RED	#-2232055-#	#-2232057-#	#-2232056-#	#-2232058-#	
BLUE	#-2232047-#	#-2232049-#	#-2232048-#	#-2232050-#	
YELLOW	#-2232063-#	#-2232065-#	#-2232064-#	#-2232066-#	
BALCK	#-2232059-#	#-2232061-#	#-2232060-#	#-2232062-#	
GREY	#-2232067-#	#-2232069-#	#-2232068-#	#-2232070-#	
GREEN	#-2232051-#	#-2232053-#	#-2232052-#	#-2232054-#	
PURPLE	#-2232071-#	#-2232073-#	#-2232072-#	#-2232074-#	
WHITE	#-2232298-#	#-2232300-#	#-2232299-#	#-2232301-#	


COLOR	PART NUMBER OF THE CONNECTOR		COMMENTS
	WITH BRIGHT PLATING CONTACT		
NATURAL	#-2232924-#	#-2232925-#	THE KEYING , POLARIZATION AND LATCH WINDOW CONFIGURATION ARE SAME AS THE MATT TIN CONNECTOR WITH THE SAME PREFIX AND POSTFIX FOR EACH COLOR. FOR EXAMPLE: 2232924-4 AND 2232043-4 HAVE SAME KEYING , POLARIZATION AND LATCH WINDOW CONFIGURATION. 2232925-4 AND 2232045-4 HAVE SAME KEYING , POLARIZATION AND LATCH WINDOW CONFIGURATION. THE DETAIL KEYING , POLARIZATION AND LATCH WINDOW CONFIGURATION FOR EACH P/N, PLEASE SEE SHEET 2-5
RED	#-2232926-#	#-2232927-#	
BLUE	#-2232928-#	#-2232929-#	
YELLOW	#-2232930-#	#-2232931-#	
BALCK	#-2232932-#	#-2232933-#	
GREY	#-2232934-#	#-2232935-#	
GREEN	#-2232936-#	#-2232937-#	
PURPLE	#-2232938-#	#-2232939-#	
WHITE	#-2232940-#	#-2232941-#	

FOR EXAMPLE, IF A CONNECTOR WITH THE CONFIGURATION AS BELOW, AND WITH TIN PLATING CONTACT, IN THE SHEET 4, WE CAN FIND THE RELATED CONNECTOR P/N WITH NATURAL COLOR IS 1-2232043-4, THEN WE CAN LOOK IN THE ABOVE TABLE TO FIND THE CONNECTOR P/N WITH RED COLOR IS 1-2232055-4



1-2232043-4

FOR ANOTHER EXAMPLE, IF A CONNECTOR WITH THE CONFIGURATION AS BELOW, AND WITH TIN PLATING CONTACT, IN THE SHEET 4, WE CAN FIND THE RELATED CONNECTOR P/N WITH NATURAL COLOR IS 1-2232045-4, THEN WE CAN LOOK IN THE ABOVE TABLE TO FIND THE CONNECTOR P/N WITH RED COLOR IS 1-2232057-4



1-2232045-4