


DO NOT SCALE

DIMENSIONS IN mm


METRIC

THIRD ANGLE

PROJECTION




LTR.	REVISION RECORD	DR.	CHK.	DATE
A1	PLATING DURAGOLD OR GOLD ALTERNATIVELY USABLE	MAH.	STRE.	13-JUN-03
-	-	-	-	-
-	-	-	-	-
-	-	-	-	-




NOTES

- 1 SNAP-IN POLARIZERS PN. 927636-2 OR 927637-2 CAN BE APPLIED.
- 2 THERE IS NO WINDOW FOR SNAP-IN POLARIZERS AT THIS END IN 10 AND 14 POS. HEADERS.
- 3 INDICATION OF FIRST POSITION.



RECOMMENDED PCB-HOLE PATTERN



2 PIN-CONTACT

BRASS

MATING SIDE: 1,2µm AU
OR 1,2µm AMP DURAGOLD®/
OVER 1,27µm NI
SOLDER SIDE: MIN. 3,0µm SN
OVER 1,27µm NI

1 HOUSING

GLASSFILLED POLYESTER

GREY

FINISH

MATERIAL

PARTNUMBER

CUSTOMER
DRAWING

FOR REFERENCE ONLY
WILL NOT BE UPDATED

DR. R HOGEVEEN DATE 08-11-89

CHK. R VERSTIJNEN DATE

APP. L.v. SOEST DATE

WIRE RANGE

INSUL. RANGE

SIZE A3

SHEET 1 OF 1

NAME AMP-HOLLAND B.V.
's-Hertogenbosch, The Netherlands.
THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION 19-
© COPYRIGHT 19- BY AMP-HOLLAND B.V.
ALL INTERNATIONAL RIGHTS RESERVED.
AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR
PATENTS PENDING.
AMP-LATCH HEADERS 180 DEG. VERSION
WITH LATCHES
C-216797
REV. DATE D M Y 08 11 89
REV. LTR. A1

100,6	90,4	96,5	86,4	78,7	64	6-216797-4
95,5	85,3	91,4	81,3	73,7	60	6-216797-0
82,8	72,6	78,7	68,6	61,0	50	5-216797-0
70,1	59,9	66,0	55,9	48,3	40	4-216797-0
62,5	52,3	58,4	48,3	40,6	34	3-216797-4
52,3	42,2	48,3	38,1	30,5	26	2-216797-6
44,7	34,5	40,6	30,5	22,9	20	2-216797-0
39,6	29,5	35,6	25,4	17,8	16	1-216797-6
37,1	26,9	33,0	22,9	15,2	14	1-216797-4
32,0	21,8	27,9	17,8	10,2	10	1-216797-0
DIM. "E"	DIM. "D"	DIM. "C"	DIM. "B"	DIM. "A"	NR. OF POSITIONS	PARTNUMBER
VARIABLE CONNECTOR DIMENSIONS						

8

7

6

5

4

3

2

1