







SIZE	Part Number	Jack Screw Thread	Packing
25	8655MH2501LF	UNC 4-40	bulk : Qty 60
	8655MH2511LF		individual set 50 sets/carton
	8655MH2502LF	M3	bulk : Qty 60
	8655MH2512LF		individual set 50 sets/carton

NOTE:RoHS INFORMATIONS

-The LF product meets European union Directives and other country regulations as described in GS-22-009

-The product is not intended to be exposed to a manufaturing solder process

-Packaging spec:see GS-14-920



NOTES : for every sizes

Material and finish : Zinc die-cast
nickel plated


Cable strain relief : Zinc die-cast

Jackscrew : Brass, nickel plated
UNC 4-40 or M3 (see tables)

Temperature range : -55°C to +125 °C






Attenuation factor : >40 dB between 10 MHz


Other size details : see on next pages.

spec ref		dr		A Parrenin	2009/05/20	projection 	mm 	size	A3	scale	3:2				
tolerance std ISO 406 ISO 1101	TOLERANCES UNLESS OTHERWISE SPECIFIED	eng	J Dalibard	2015/09/10	ecn no			ELX-B-20414-1							
		chr	J Dalibard	2015/09/10											
		appr	Aymeric Soudy		2015/09/11	product family		-	rel level	Released					
surface - ✓ ISO 1302	linear	0.X	± /			title	STRAIGHT METAL HOODS WITH 2 METAL CLAMPS				dwg no	C-8655-1685C		rev	D
		0.XX	± /												
		0.XXX	± /												
	angular	0°	± / °		www.fci.com	cat. no.	-	Product - Customer Drw				sheet 1 of 4			

SIZE	Part Number	Jack Screw Thread	Packing
09	8655MH0901LF	UNC 4-40	bulk : Qty 80
	8655MH0911LF		individual set 50 sets/carton
	8655MH0902LF	M3	bulk : Qty 80
	8655MH0912LF		individual set 50 sets/carton

SIZE	Part Number	Jack Screw Thread	Packing
15	8655MH1501LF	UNC 4-40	bulk : Qty 80
	8655MH1511LF		individual set 50 sets/carton
	8655MH1502LF	M3	bulk : Qty 80
	8655MH1512LF		individual set 50 sets/carton



spec ref				dr	A Parrenin	2009/05/20	projection		mm		size	A3	scale	3:2
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	J Dalibard	2015/09/10					ecn no	ELX-B-20414-1		
				chr	J Dalibard	2015/09/10								
ISO 406 ISO 1101				appr	Aymeric Soudy	2015/09/11	product family		-	rel level	Released			
surface 	linear	0.X	±/		title	STRAIGHT METAL HOODS WITH 2 METAL CLAMPS			dwg no	C-8655-1685C		rev	D	
		0.XX	±/											
		0.XXX	±/											
ISO 1302	angular	0°	±/°	www.fci.com	cat. no.	-	Product - Customer Drw				sheet 2 of 4			



Copyright FCI.



A

B

C



D

SIZE	Part Number	Jack Screw Thread	Packing
37	8655MH3701LF	UNC 4-40	bulk : Qty 40
	8655MH3711LF		individual set 50 sets/carton
	8655MH3702LF	M3	bulk : Qty 40
	8655MH3712LF		individual set 50 sets/carton



PRODUCT WITH
M3 THREAD
JACKSCREWS

SIZE	Part Number	Jack Screw Thread	Packing
50	8655MH5001LF	UNC 4-40	bulk : Qty 40
	8655MH5011LF		individual set 50 sets/carton
	8655MH5002LF	M3	bulk : Qty 40
	8655MH5012LF		individual set 50 sets/carton



A

B


C

D

spec ref				dr	A Parrenin	2009/05/20	projection	mm	size	A3	scale	3:2		
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	J Dalibard	2015/09/10			ecn no	ELX-B-20414-1				
				chr	J Dalibard	2015/09/10								
				appr		Aymeric Soudy						2015/09/11	product family	
surface	ISO 406 ISO 1101	linear	0.X	±/		title	STRAIGHT METAL HOODS			dwg no	C-8655-1685C		rev	D
			0.XX	±/										
			0.XXX	±/										
		ISO 1302	angular	0°	±/°	www.fci.com	cat. no.	-	Product - Customer Drw			sheet 3 of 4		


CABLING INSTRUCTIONS

1- Strip the cable and solder or crimp the wires




SCALE 3:2

2-Put the connector into a half hood and tighten the jacket with a metal clamp




SCALE 3:2

3-To get the electrical continuity between the cable outer conductor and the hood tighten the outer conductor with the other metal clamp as shown



SCALE 3:2

4-Mount the jackscrews, the other half hood and tighten with 2 screws



Copyright FCI.

spec ref				dr		A Parrenin	2009/05/20		projection		mm		size		A3	scale		1:1							
tolerance ref std		TOLERANCES UNLESS OTHERWISE SPECIFIED				eng		J Dalibard	2015/09/10						ecn no				ELX-B-20414-1						
ISO 406						chr		J Dalibard	2015/09/10						rel level				Released						
ISO 1101						appr		Aymeric Soudy		2015/09/11									product family						
surface						linear				title		STRAIGHT METAL HOODS WITH 2 METAL CLAMPS				dwg no		C-8655-1685C				rev		D	
		0.X		±/																					
		0.XX		±/																					
		ISO 1302		angular		0°		±/°		www.fci.com		cat. no.				Product - Customer Drw				sheet 4 of 4					