

TECHNICAL DATA SHEET
ARC RESONANT ABSORBER
ARC - UD - 11091

Description: Flexible, ferrite loaded urethane rubber based microwave absorber tuned for mode suppression in an enclosed cavity, signal isolation and surface current attenuation. It can be provided with or without pressure sensitive transfer adhesive on the back side.

Sheet Size: 12" x 12" or 24" x 24"

Part Size: Can be die cut or waterjet cut to many Configurations.


Thickness: .200" +/- .005

Color: Gray

Temperature Range: -60F to +275F

Outgassing Properties:	TML	CVCM Recovered	Water Vapor
	<1.0%	<.10%	.07

Reflection Loss 20dB at 2GHz (Typical):



The technical information contained herein is consistent with the properties of this material but should not be used in the preparation of specifications as it is intended for reference only.



Solutions for Interference Control

ARC Technologies, Inc.
11 Chestnut Street, Amesbury, MA 01913
978-388-2993 Fax: 978-388-6866
www.arc-tech.com