

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC
ADDIST
25

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	0	RELEASED PER EC 0S12-0061-05	06APR05	JDP	AMS

1. SUITABLE FOR MALE TYPE M CONNECTORS.

2 RETAINING RING.

3 GOLD PLATE 0.000762 [.000030] MIN THICK IN ZONE 1, TIN PLATE
0.00254 [.000100] MIN THICK IN ZONE 2. NICKLE UNDERPLATE
0.00127 [.000050] MIN THICK ALL OVER.

3

CONTACT; COPPER ALLOY
RETAINING RING; COPPER ALLOY

5148354-1

FINISH

MATERIAL

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
J. POLIGNONE 06APR05CHK
A. SHARPE 06APR05APVD
A. SHARPE 06APR05

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

tyco
ElectronicsTyco Electronics Corporation
Harrisburg, Pa 17105-3608NAME
POWER CONTACT, MALE, RIGHT ANGLE
4 SOLDER POSTS
(25 AMP)SIZE
A300779CAGE CODE
C-5148354

DRAWING NO

RESTRICTED TO

SCALE
5:1SHEET
1 OF 1REV
0DIMENSIONS:
mm [INCHES]TOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ± -
1 PLC ± -
2 PLC ± 0.13 [.005]
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISHMATERIAL
SEE TABLE

SEE TABLE