

Tyco / Electronics
Raychem Circuit Protection
 308 Constitution Drive
 Menlo Park, CA 94025-1164
 Phone: 800-227-4856
 Fax: 800-227-4866

PolySwitch®
PTC Devices
 Overcurrent Protection Device

PRODUCT:LR4-190

DOCUMENT: SCD 23745
 PCN: 638885
 REV LETTER: D
 REV DATE: AUGUST 26, 2002
 PAGE NO: 1 OF 1

Specification Status: Released

Electrical Rating

Voltage: 15Vdc MAX

Current: 100A MAX

Leads:

Nickel: 0.13mm nom.

Tape:

Polyester

Marking:

— Manufacturer's Mark
 ✕ E19 — Part Identification
 □ □ □ □ — Lot Identification




TABLE I. DIMENSIONS:

	A		B		C		D		E		F		G	
	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX
mm:	19.9	22.1	4.9	5.5	0.6	1.0	5.5	7.5	5.5	7.5	3.9	4.1	--	--
in*:	(0.78)	(0.87)	(0.19)	(0.22)	(0.02)	(0.04)	(0.22)	(0.30)	(0.22)	(0.30)	(0.15)	(0.16)	--	--

*Rounded off approximation

TABLE II. PERFORMANCE RATINGS:

I HOLD	CURRENT TRIP LIMITS								TIME TO TRIP		REFERENCE RESISTANCE		ONE-HOUR POST-TRIP RESISTANCE		TRIPPED-STATE POWER DISSIPATION
AMPS 20°C HOLD	AMPS AT 0°C HOLD TRIP		AMPS AT 20°C HOLD TRIP		AMPS AT 60°C HOLD TRIP		AMPS AT 80°C HOLD TRIP		SECONDS AT 20°C, 9.5 A TYP MAX		OHMS AT 20°C MIN MAX		OHMS AT 20°C MIN MAX		WATTS AT 20°C, 15V MAX
1.9	2.3	4.6	1.9	3.9	1.4	2.8	--	--	--	5	0.039	0.072	0.039	0.102	1.2

Reference Documents:

Precedence:

Effectivity:

CAUTION:

PS300

This specification takes precedence over documents referenced herein.

Reference documents shall be the issue in effect on the date of invitation for bid.

Operation beyond the rated voltage or current may result in rupture, electrical arcing or flame.

OBSELETE
NOT the LATEST
REVISION