



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AJ	16		A	REV PER ECO 07-006131	15MAR2007	DW	JL



PCB CONFIGURATION
TOLERANCE = ±0.08 [.003]

- 1 ZINC PER QQ-Z-363.
- 2 PHOSPHOR BRONZE PER QQ-B-750.
- 3 POLYMETHYLPENTENE AND ACETAL, GENERAL PURPOSE.
- 4 MATTE TIN PLATE PER ASTM-B-545, 3.81 μm [.000150] MINIMUM THICK.
- 5. CONNECTOR WILL ACCEPT A CENTER CONDUCTOR DIAMETER RANGE OF 0.56 [.022] – 1.19 [.047].
- 6 LOGO WILL BE LOCATED ON SURFACE INDICATED.
- 7 MAJOR DIA MODIFIED TO .363 REF.
- 8 BRIGHT TIN PLATE PER ASTM-B-545, 3.81 μm [.000150] MINIMUM THICK.

8	6274020-2
4	6274020-1
SHELL FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. VARELA — 01FEB2005 DOCK5		tyco Electronics Tyco Electronics Corporation Harrisburg, Pa 17105-3608					
DIMENSIONS: mm [INCHES]		CHK J. HAVENER 01FEB2005							
	TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.20 [.008] 3 PLC ± - 4 PLC ± - ANGLES ± ±	APVD K. WEIDNER 01FEB2005		NAME JACK, VERT, PCB, F SERIES - -					
		PRODUCT SPEC —							
		APPLICATION SPEC —		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
		MATERIAL 	FINISH SEE TABLE	WEIGHT —	A2	00779	C=6274020	—	
CUSTOMER DRAWING				SCALE	6:1	SHEET	1 of 1	REV	A