

PRODUCT NUMBER
10075025-XXX-XXXLF

PLATING

S = 0.38μm GOLD/GXT ON CONTACT AREA
2μm MIN MATTE TIN ON TAIL

G = 0.76μm GOLD/GXT ON CONTACT AREA
2μm MIN MATTE TIN ON TAIL

F = GOLD FLASH ON CONTACT AREA
2μm MIN MATTE TIN ON TAIL

1.27 μ m MIN NICKEL UNDERPLATING

PIN STYLE	TAIL LENGTH	MISSING PIN POSITION
01	2.00	
02	2.50	
03	2.00	A01

NOTES:

1. MATERIAL HOUSING: HIGH TEMP. THERMOPLASTIC
UL 94V-0, COLOR NATURAL

- ## 2. MATERIAL TERMINAL: COPPER ALLOY

3. TO DETERMINE DIMENSIONS:
N = NUMBER OF POSITIONS PER ROW

4. 7N MIN. PIN RETENTION IN EITHER DIRECTION.

5. PACKAGING:

= STANDARD PACKAGING IN POLYBAG

U = TUBE AVAILABLE FROM 03 TO 25 POS PER ROW

A = TAPE & REEL WITH PICK UP CAP INSTALLED
SEE TA-884 FOR PRODUCT AVAILABILITY

- ## 6. POLARIZATION :

- SEE TABLE FOR AVAILABILITY
- FOR NEW REQUEST, PLEASE TO CONTACT FCI

- ## 7. RoHS COMPATIBLE PRODUCT SPECIFICATIONS

- a - PLATING:

- "LF" MEANS THE PRODUCT IS LEAD-FREE,
2μm MINIMUM MATTE TIN OVER 1.27μm
MINIMUM NICKEL UNDERPLATE.

- b - MANUFACTURING PROCESS COMPATIBILITY

- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 30 SECONDS MAX IN A CONVECTION, INFRA-RED, OR VAPOR PHASE OR REFLOW OVEN

- c - LABELLING:


- MEETS PACKAGING SPECS AS PER GS-14-920

- d - LEGAL STATEMENT : SEE GS-47-0004


LEAD FREE
RoHS COMPATIBLE
NOTE 7

PACKAGING NOTE 5

TOTAL NUMBER OF
POSITIONS 04 TO 50



SECTION A-A



RECOMMENDED 1.6mm THICK PCB LAYOUT
STENCIL DESIGN RECOMMENDATIONS
AS PER TA-896









mat'l. code				surface ISO 1302 ☒		tolerance ISO 406 ISO 1101		projection 		product family MINITEK			
ltr		ecn no		dr		date		tolerances unless otherwise specified		title			
H		B-19190		LMU		14.10.24		angles linear .X ±0.3 .XX ±0.15 .XXX ±0.05		mm →		UNSHR.HEADER 2.00 mm VERTICAL PIP	
J		B-19408		AMA		14.11.12							
K		B-19797		AMA		14.12.16							
L		B-20024		BVE		15.01.20		dr		L MULIN		07.01.04	
M		B-20079		AMA		15.01.23		enrg		J.COMPAGNON		07.01.04	
N		B-20254		LMU		15.02.16		chr					
P		B-21209		AMA		15.06.22		appd		JM.C		07.01.04	
sheet index		revision sheet		P		B							
				1		2							



FCIconnect.com

Copyright FCI

2x3 POS AND 2x4 POS CONFIGURATION
NO LATCHING AVAILABLE FOR 2x2 POS



2x5 POS UP TO 2x25 POS CONFIGURATION

LATCHING FEATURES WHEN USED IN COMBINATION
WITH ACTIVE LATCH HOUSING 10073599

mat'l. code				surface	tolerance	projection	product family
				ISO 1302	ISO 406 ISO 1101		MINITEK
ltr	ecr no	dr	date	tolerances unless otherwise specified			title
A	F06-0113	LMU	08.01.07	angles	.X ±0.3	mm	UNSHR.HEADER
B	B-17556	JCO	14.04.23	linear	.XX ±0.15	mm	2.00 mm VERTICAL PIP
					.xxx ±0.05	scale 5:1	dwg no
				dr	L MULIN	07.12.04	sheet 2 of 2
				enr	J.COMPAGNON	07.12.04	size
				chr			10075025
				appd	JM.C	07.12.04	A3
sheet	revision						type
index	sheet						CUSTOMER Drawing