






3-DIMENSIONAL MODELS



1 PARTS COMPLY TO AMP SOLDERABILITY SPECIFICATION 109-11-3.

2 CONTACT IS PLATED OVERALL WITH 0.00127 [.000050] NICKEL, THEN 0.00076 [.000030] GOLD OVER CONTACT LENGTH INDICATED AND MATTE TIN LEAD ON SOLDER TAIL END.

3 CIRCUIT IDENTIFICATION CHARACTERS ARE ADJACENT TO THE INDICATED CAVITIES, BUT LOCATION AND ORIENTATION MAY DIFFER FROM PRINT.

4 DIMENSIONS IN BRACKETS ARE IN INCHES.

5 CONTACT IS PLATED OVERALL WITH 0.00127 [.000050] NICKEL, THEN 0.00076 [.000030] GOLD OVER CONTACT LENGTH INDICATED AND MATTE TIN ON SOLDER TAIL END.

6 SUPERSEDED BY 640466-3

6	PHOSPHOR BRONZE, GOLD Δ 5	NYLON,UL94V-2,NATURAL	640466-3
	PHOSPHOR BRONZE, GOLD Δ 2	NYLON,UL94V-2,NATURAL	640466-2
	PHOSPHOR BRONZE, PRE-TIN	NYLON,UL94V-2,NATURAL	640466-1
	PIN CONTACT MATERIAL AND FINISH	HOUSING MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. LEWIS 10-05-98 CHK R. SWING 10-05-98 APP'D M. TRULL 10-05-98	 TE Connectivity
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME	
	0 PLC ± - 1 PLC ± - 2 PLC ± ± 0.13 [005] 3 PLC ± - 4 PLC ± - ANGLES ± 0°30'	PRODUCT SPEC - APPLICATION SPEC - WEIGHT -	PIN HEADER ASSEMBLY, 5 CIRCUIT UNIVERSAL MATE-N-LOK™
	MATERIAL	FINISH	SIZE A1
	SEE TABLE	SEE TABLE	GAGE CODE 00779
			DRAWING NO C-640466
CUSTOMER DRAWING		SCALE 5:1	SHEET 1 OF 1 REV M