





ENG. NO. 0*04
SD-70021-0*21

EDP NO. #

適用電線表示
CRIMP SIZE CODE LETTER







断面 A-A
SECTION A-A
(SCALE:20-1)



注記:
NOTES:

- 1. 適合ハウジング: 70066-****, 70107-****
APPLICABLE HOUSING: 70066-****, 70107-****
- 2. 仕上げ ニッケル下地、錫メッキ
FINISH TIN OVER NICKEL PLATING

1.91	2.1	1.47	1.22	A	ø 1.6 MAX.	AWG#24-#30	バラ状 LOOSE	70021-0204
							連鎖状 CHAIN	70021-0004
1.91	2.1	1.65	1.84	C		AWG#22-#24	バラ状 LOOSE	70021-0221
							連鎖状 CHAIN	70021-0021
D	C	B	A	適用電線表示 CRIMP SIZE CODE LETTER	被覆外径 INS. RANGE	適用電線範囲 WIRE RANGE	端子形状 FORM	MATERIAL No.
					材料 MATERIAL	燐青銅 PHOSPHOR BRONZE t 0.203	MOLEX-JAPAN CO.,LTD. 日本モレックス株式会社	
					仕上げ FINISH	注記参照 SEE NOTES	EDP. NO. ———	
B	変更 REVISED	(J2004-45)9	Y.W M.S	84/05/3	適用電線範囲 WIRE RANGE	表参照 SEE CHART	ENG. NO.	REV
A	変更 REVISED	(T2015)9	H.H H.I	91/5/28	被覆外径 INS. RANGE	表参照 SEE CHART	SD-70021- 0*04 0*21	B
0	新規作成 RELEASED	(T010)10	A.M M.S	98/4/6	DRAWN BY CHK'D BY	A. Mitake H. Arita	TITLE 名称 SL MALE CRIMP TERMINAL -LEAD FREE-	
記号 LTR	変更内容 REVISION RECORD	DR.	CHK.	日付 DATE	APP'D BY S. Yamada	尺度 SCALE 10-1		
REVISE ONLY ON CAD SYSTEM								



NOTES:

1. TERMINAL FOR USE WITH HOUSING PART NO. 70066-**** & 70107-****.
2. MATERIAL: .008/(0.20) THK. PHOSPHOR BRONZE.
3. TERMINAL TO BE USED WITH 24-30 AWG STRANDED WIRE WITH .060 DIA. MAX. INSULATION.
4. REFER TO MOLEX OPERATIONAL AND SERVICE MANUAL FOR DETAILS.
5. REFER TO PRODUCT SPECIFICATION NO. PS-70021.
6. PARTS SUPPLIED LOOSE PER DRAWING PK-70873-0822.

PLATING:

.000150 MIN. TIN PLATE
OVER NICKEL PLATE.

*THE PRIMARY SHIPPING CARTON WILL BE LABELED "COMPLIANT TO
RoHS DIRECTIVE 2002/95/EC AND ELV ANNEX II OF DIRECTIVE 2000/53/EC".
CARTONS WITHOUT THIS LABEL MAY CONTAIN PRODUCT WITH LEAD.

D	LEAD FREE UCP2004-1769 RWHITE 04/03/15
C2	REVISED PER ECR #U80270 MCGRATH 97/07/31
C1	REVISED PER ECR #U70928 MCGRATH 97/06/26
C	164 PLTG. WAS 102 PER ECR # U31149 08/19/93 REED
B	REDRAWN ON CAD PER ECR # 9509 11/10/86 WJF/MJM

MFG.	SH.	REV.	LTR.	REVISIONS
------	-----	------	------	-----------

DIMENSIONS SHOWN (METRIC) INCH		▽ = 0 ▼ = 0		REVISE ONLY ON CAD SYSTEM	
UNLESS OTHERWISE SPECIFIED TOLERANCES: ANGULAR ± 1/2°					
INCH		METRIC			
3 PLACE	± .010	---			
2 PLACE	± .015	± 0.25			
1 PLACE	---	± 0.35			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS					
DRWG. BY	WJF	CHK'D. BY	MJM		
APP'D. BY	WAZ	SCALE	10: 1		
FILE NAME S70021X4 DGN		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.		DIV. DA	SIZE B

TITLE TERMINAL, MALE CRIMP	
MOLEX INCORPORATED LISLE, ILL. 60532 U.S.A.	SHEET NO. 1 DATE 10/30/86
PART NO. 16-02-0108	DRWG. NO. SD-70021-0204