




13		12		11		10		9		8		7		6		5		4		3		2		1	
J	CKT. SIZE	PART NUMBER	ENG. NUMBER SDA-70204-	DIM. "A"		DIM. "B"		DIM. "C"		J	CKT. SIZE	PART NUMBER	ENG. NUMBER SDA-70204-	DIM. "A"		DIM. "B"		DIM. "C"		I					
				MM	IN.	MM	IN.	MM	IN.					MM	IN.	MM	IN.	MM	IN.						
	08	25-02-5008	0899	7,62	.300	17,78	.700	20,32	.800		42	25-02-5042	0916	50,80	2.000	60,96	2.400	63,50	2.500						
	10	25-02-5010	0900	10,16	.400	20,32	.800	22,86	.900		44	25-02-5044	0917	53,34	2.100	63,50	2.500	66,04	2.600						
	12	25-02-5012	0901	12,70	.500	22,86	.900	25,40	1.000		46	25-02-5046	0918	55,88	2.200	66,04	2.600	68,58	2.700						
	14	25-02-5014	0902	15,24	.600	25,40	1.000	27,94	1.100		48	25-02-5048	0919	58,42	2.300	68,58	2.700	71,12	2.800						
	16	25-02-5016	0903	17,78	.700	27,94	1.100	30,48	1.200		50	25-02-5050	0920	60,96	2.400	71,12	2.800	73,66	2.900						
	18	25-02-5018	0904	20,32	.800	30,48	1.200	33,02	1.300		52	25-02-5052	0921	63,50	2.500	73,66	2.900	76,20	3.000						
I	20	25-02-5020	0905	22,86	.900	33,02	1.300	35,56	1.400		54	25-02-5054	0922	66,04	2.600	76,20	3.000	78,74	3.100						
	22	25-02-5022	0906	25,40	1.000	35,56	1.400	38,10	1.500		56	25-02-5056	0923	68,58	2.700	78,74	3.100	81,28	3.200						
	24	25-02-5024	0907	27,94	1.100	38,10	1.500	40,64	1.600		58	25-02-5058	0924	71,12	2.800	81,28	3.200	83,82	3.300						
	26	25-02-5026	0908	30,48	1.200	40,64	1.600	43,10	1.700		60	25-02-5060	0925	73,66	2.900	83,82	3.300	86,36	3.400						
	28	25-02-5028	0909	33,02	1.300	43,10	1.700	45,72	1.800		62	25-02-5062	0926	76,20	3.000	86,36	3.400	88,90	3.500						
	30	25-02-5030	0910	35,56	1.400	45,72	1.800	48,26	1.900		64	25-02-5064	0927	78,74	3.100	88,90	3.500	91,44	3.600						
H	32	25-02-5032	0911	38,10	1.500	48,26	1.900	50,80	2.000		66	25-02-5066	0928	81,28	3.200	91,44	3.600	93,98	3.700						
	34	25-02-5034	0912	40,64	1.600	50,80	2.000	53,34	2.100		68	25-02-5068	0929	83,82	3.300	93,98	3.700	96,52	3.800						
	36	25-02-5036	0913	43,10	1.700	53,34	2.100	55,88	2.200		70	25-02-5070	0930	86,36	3.400	96,52	3.800	99,06	3.900						
	38	25-02-5038	0914	45,72	1.800	55,88	2.200	58,42	2.300		72	25-02-5072	0931	88,90	3.500	99,06	3.900	101,60	4.000						
	40	25-02-5040	0915	48,26	1.900	58,42	2.300	60,96	2.400																





DETAIL "V"
SCALE = 20:1



DETAIL "S"



SECTION W-W



- NOTES:
1. WAFER MATERIAL: GLASS FILLED NYLON, COLOR: BLACK
2. PIN MATERIAL: COPPER ALLOY
3. PIN PLATING:
OVERALL: 150 MICROINCHES MINIMUM TIN
OVER NICKEL UNDERPLATE
4. PINS MUST MEET SOLDERABILITY SPEC. NO. 152
5. PIN PUSH-OUT FORCE (1.81 KG/4 LBS MINIMUM
6. REFER TO P.S. NO. 70204
7. STANDARD PACKAGING PER: PK-70873-0070

CORRECT DIMENSION EC NO: UCP2011-3892 DRAWN:MS BARRA CHKD:DMORGAN APPR:SMILLER REV: 1	DESCRIPTION 2011/06/27 2011/07/07	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 4:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		
				mm	INCH	DRAWN BY JAS		DATE 1986/05/20		TITLE SHROUDED HEADER DUAL ROW W/PCB SLOTS & GUIDE EARS .100 GRID, .025 SQ PIN molex MOLEX INCORPORATED	
			4 PLACES	± ---	± ---	CHECKED BY EIK		DATE 1986/05/20			
			3 PLACES	± ---	± .010	APPROVED BY WAZ		DATE 1986/05/20			
			2 PLACES	± ---	± ---						
			1 PLACE	± ---	± ---	MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
			ANGULAR ±1/2°			SEE TABLE		SDA-70204-0897-0960		1 OF 1	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								