

W503IDT HIGH EFFICIENCY RED


### Features

- LOW POWER CONSUMPTION.
- WIDE VIEWING ANGLE.
- RELIABLE AND RUGGED.
- EXCELLENT UNIFORMITY OF LIGHT OUTPUT.
- IDEAL AS FLUSH MOUNTED PANEL INDICATORS.
- LONG LIFE - SOLID STATE RELIABILITY.

### Description

The High Efficiency Red source color devices are made with Gallium Arsenide Phosphide on Gallium Phosphide Orange Light Emitting Diode.

### Package Dimensions



#### Notes:

1. All dimensions are in millimeters (inches).
2. Tolerance is  $\pm 0.25(0.01)$  unless otherwise noted.
3. Lead spacing is measured where the lead emerge package.
4. Specifications are subject to change without notice.

## Selection Guide

| Part No. | Dice                           | Lens Type    | Iv (mcd)<br>@10 mA |      | Viewing<br>Angle |
|----------|--------------------------------|--------------|--------------------|------|------------------|
|          |                                |              | Min.               | Typ. | 2θ1/2            |
| W503IDT  | HIGH EFFICIENCY RED(GaAsP/GaP) | RED DIFFUSED | 3                  | 6    | 110°             |

Note:

1. θ1/2 is the angle from optical centerline where the luminous intensity is 1/2 the optical centerline value.

## Electrical / Optical Characteristics at T<sub>A</sub>=25°C


| Symbol            | Parameter                | Device              | Typ. | Max. | Units | Test Conditions            |
|-------------------|--------------------------|---------------------|------|------|-------|----------------------------|
| λ <sub>peak</sub> | Peak Wavelength          | High Efficiency Red | 627  |      | nm    | I <sub>F</sub> =20mA       |
| λ <sub>D</sub>    | Dominate Wavelength      | High Efficiency Red | 625  |      | nm    | I <sub>F</sub> =20mA       |
| Δλ <sub>1/2</sub> | Spectral Line Half-width | High Efficiency Red | 45   |      | nm    | I <sub>F</sub> =20mA       |
| C                 | Capacitance              | High Efficiency Red | 15   |      | pF    | V <sub>F</sub> =0V; f=1MHz |
| V <sub>F</sub>    | Forward Voltage          | High Efficiency Red | 2.0  | 2.5  | V     | I <sub>F</sub> =20mA       |
| I <sub>R</sub>    | Reverse Current          | High Efficiency Red |      | 10   | uA    | V <sub>R</sub> = 5V        |

## Absolute Maximum Ratings at T<sub>A</sub>=25°C

| Parameter                     | High Efficiency Red | Units |
|-------------------------------|---------------------|-------|
| Power dissipation             | 105                 | mW    |
| DC Forward Current            | 30                  | mA    |
| Peak Forward Current [1]      | 160                 | mA    |
| Reverse Voltage               | 5                   | V     |
| Operating/Storage Temperature | -40°C To +85°C      |       |
| Lead Solder Temperature [2]   | 260°C For 5 Seconds |       |

Notes:

- 1/10 Duty Cycle, 0.1ms Pulse Width.
- 2mm below package base.



## High Efficiency Red W503IDT

