

No.420-R Stationary Caster



■ Specification

Rubber wheel

Model No.	Allowable Load(kg)	Net Weight(g)	Code No.	
No.420-R-R25-1	8	26	9719	
No.420-R-R32-2	12	35	9720	
No.420-R-R38-3	20	60	9721	
No.420-R-R50-4	30	130	9722	
No.420-R-R65-5	40	230	9723	
No.420-R-R75-6	50	310	9724	

Nylon wheel

Model No.	Allowable Load(kg)	Net Weight(g)	Code No.	
No.420-R-N25-1	10	25	9731	
No.420-R-N32-2	18	30	9732	
No.420-R-N38-3	28	50	9733	
No.420-R-N50-4	38	100	9734	
No.420-R-N65-5	55	170	9735	
No.420-R-N75-6	65	200	9736	

Casting wheel

Model No.	Allowable Load(kg)	Net Weight(g)	Code No.	
No.420-R-C25-1	12	45	9725	
No.420-R-C32-2	20	55	9726	
No.420-R-C38-3	30	112	9727	
No.420-R-C50-4	40	200	9728	
No.420-R-C65-5	60	460	9729	
No.420-R-C75-6	70	540	9730	

Wheel	R-Rubber wheel
	C-Casting wheel
	N-Nylon wheel

■ Size List

No.	D	G	H	J	L1	L2	P1	P2	W		
									Rubber Wheel	Casting Wheel	Nylon Wheel
1	φ 25	φ 4.2	35	t1.6	18	36	—	29	12	12	12
2	φ 32		42		20				14	14	14
3	φ 38	φ 5.3	50	t1.8	25	46	15	36	17	17	16
4	φ 50	φ 6.5	65	t2.0	40	58	25	45	20	21	21
5	φ 65	φ 8.8	80	t2.3	47	70	28	55	26	25	25
6	φ 75		90								



■ Characteristic

Choose one of caster from wide variety of selection with material and size of wheels.

■ Application

Medium or small size devices / working platforms.

No.420-R-25~No.420-R-38



No.420-R-50~No.420-R-75

