







REV.	DATE	DESCRIPTION
A	03/27/05	UPDATE DRAWING FORMAT



RECOMMENDED
MOUNTING HOLE



RECOMMENDED CABLE
STRIPPING DIMS.



NOTES:

1. CRIMPED FERRULE
HEX CRIMP SIZE .128"
2. MAX. PANEL THICKNESS = 2.4mm

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.60mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex								
8						DRAWN	G.R.S.	03/27/05										
7	HEAT SHRINK TUBE			1		CHECKED												
6	HEX NUT	BRASS	GOLD	1		ISSUED												
5	LOCK WASHER	BRASS	GOLD	1		SHEET	1 OF 1											
4	FERRULE	COPPER	GOLD	1														
3	CONTACT PIN	BRASS	GOLD	1														
2	INSULATOR	TEFLON	NATURAL	1					PART DESCRIPTION									
1	BODY	BRASS	GOLD	1					SMC BULKHEAD CRIMP JACK (FOR RG-174/U, 188A/U, 316/U)									
									PART NO.									
									152105									
					CAD FILE C:/152/152105.DWG				DWG. NO.		152105.DWG		REV.	A	SIZE	A	SCALE	NA