
## Subminiature Coaxial Switch 1.6 mm High, DC to 6 GHz

MS-156HF Series

**Halogen Free** 



### Features

#### 1. Low insertion loss

0.1 dB typical at 6 GHz (not mated with the plug).

### 2. Space-saving design

2.7 mm x 2.7 mm occupied board space.

### 3. Low profile

1.6 mm protrusion above the board.

#### 4. Lightweight

0.025 g. total weight (without vacuum cap).

#### 5. Durability

100 mating/unmating cycles, with corresponding plug.

### 6. Performs over a wide frequency range

Applicable frequencies range over a wide band, from DC to 6 GHz.

#### 7. Solder wicking prevention

Nickel plating barrier on the contacts prevents solder compound intrusion (wicking) into the contact engagement areas.

#### 8. Board placement with automatic equipment

Packaged on tape-and-reel. Also available with a vacuum pick-up cap over each switch.

#### 9. RoHS compliant

All components and materials comply with the requirements of the EU Directive 2002/95/EC.

### 10. Halogen Free


Chlorine, and bromine are not used in the receptacles. \*Definition according to IEC 61249-2-21. Br 900 ppm max., Cl 900 ppm max., and Br + Cl 1500 ppm max.

### Applications

Portable terminals, ETC, notebook computers (Bluetooth), wireless LAN, POS terminals, GPS terminals, PDA, and any small devices requiring verification of antenna/circuit performance.

#### Overview

Developed for inspection of high frequency circuits used in portable terminals. Verification of the circuit performance is accomplished by simply inserting the external plug in the board mounted receptacle. This action re-directs the circuit from normal condition to the plug side. Removing the plug restores circuit to its normal condition.









## **■**Specifications

	Not mated with the plug	Mated (MS-156-HRMJ-3)
Operating temperature range	-40°C to +85°C	-40℃ to +85℃
Rated power	2W	2W
Frequency range	DC to 6GHz	DC to 6GHz
Insertion loss	0.1 dB max. (DC to 2.5GHz) 0.15 dB max. (2.5GHz to 6.0GHz)	0.5 dB max. (DC to 3.0GHz) 1.2 dB max. (3.0GHz to 6.0GHz)
Isolation	20 dB max. (DC to 2.0GHz) 15 dB max. (2.0GHz to 4.0GHz) 13 dB max. (4.0GHz to 6.0GHz)	
V.S.W.R	1.2 max. (DC to 2.5GHz) 1.3 max. (2.5GHz to 6.0GHz)	1.4 max. (DC to 3.0GHz) 1.8 max. (3.0GHz to 6.0GHz)


Item	Specification	Conditions	
1. Contact resistance	100 mΩ max.	100 mA max.	
2. Insulation resistance	1000 MΩ min.	100 V DC	
3. Withstanding voltage	No flashover or insulation breakdown	100 V AC / 1 minute	
4. Vibration		Frequency:10 to 55 Hz, single amplitude of	
4. VIDIALION	No electrical discontinuity of 1 μs or more	0.75 mm, 2 hours in each of the 3 axis.	
5. Shock	Two electrical discontinuity of 1 $\mu$ s of more	Acceleration of 490 m/s <sup>2</sup> , 6 ms duration, sine half-	
5. SHOCK		wave waveform, 3 cycles in each of the 3 axis	
	Contact resistance: 100 mΩ max. Insulation resistance: 10 MΩ min.	Temperature: $-55^{\circ}\text{C} \rightarrow +5^{\circ}\text{C}$ to $+35^{\circ}\text{C} \rightarrow +85^{\circ}\text{C} \rightarrow +5^{\circ}\text{C}$ to $+35^{\circ}\text{C}$	
6. Temperature cycle		Time: $30 \rightarrow 2$ to $3 \rightarrow 30 \rightarrow 2$ to 3 (Minutes)	
	insulation resistance: 10 Mtz min.	100 cycles	
7 High tomporature expecure	Contact resistance: 100 mΩ max.	96 hours at 85℃	
7. High temperature exposure	Insulation resistance: 10 MΩ min.	90 Hours at 65 C	
0 Low tomporature evacuure	Contact resistance: 100 mΩ max.	96 hours at -55℃	
8. Low temperature exposure	Insulation resistance: 10 MΩ min.	96 Hours at -55 C	
0.11	Contact resistance: 100 mΩ max.	OC house at 10 LOS and humidity of 00 to 05%	
9. Humidity	Insulation resistance: 10 MΩ min.	96 hours at 40±2°C, and humidity of 90 to 95%	
10. Durability (mating/un-mating,	Contact resistance: 100 mΩ max.	100 avales	
with corresponding plug)	Contact resistance. Too my max.	100 cycles	

### **■**Materials


Part	Material	Finish	Remarks
Shell	Phosphor bronze	Gold plated	
Insulator	6T Nylon		UL94HB
Common terminal	Beryllium copper	Selective gold plated	
Antenna terminal	Phosphor bronze	Selective gold plated	

### **◆**Typical Data


### ●NORMALLY CLOSED(N.C)~(Not mated with the plug)



### ●OPEN(N.O)~(Mated with the plug)








### **■**Receptacle

### Without vacuum pick-up cap




Part Number	CL No.	Packaging
MS-156HF	358-0238-4	10,000 pieces/reel
MS-156HF(01)	358-0238-4-01	100 pieces/bag
MS-156HF(20)	358-0238-4-20	2,000 pieces/reel



### ●With vacuum pick-up cap





Part Number	CL No.	Packaging
MS-156HF(02)	358-0238-4-02	8,500 pieces/reel
MS-156HF(22)	358-0238-4-22	1,500 pieces/reel



Note:Vacuum pick-up cap flat can be oriented in any direction. Orientation will not affect placement of the switch on the board


### **◆Circuit diagram**






### **▶** PCB mounting pattern and metal mask dimensions

- \* Request drawing of the specific part for exact dimensions and tolerances.
- \* Specified dimensions must be followed to assure correct board placement and performance.






This area must be free of conductive traces and resist field.

### **◆**Precautions

- 1. This product is intended to be used for circuit inspection only. Consult us if any other application is considered.
- 2. Cross-hatched area shown on the PCB mounting pattern must be free of any conducive traces. Placing conductive traces in this area may affect performance and will void product warranties. When the bottom surface of the product (i.e., the shaded area of the specified land dimensions diagram on the previous page) has been processed with a susbtrate copper trace and resist processing, Hirose Electric will not be able to warrant the product.
- 3. Do not use hand soldering for mounting of MS-156HF.

  Doing so could result in solder and flux wicking to the contact areas.
- 4. Exercise caution as not to allow any debris to enter the board mounted MS-156HF when cutting PCB.


Recommended Mounting of MS-156HF coaxial switch on the PCB during the manufacturing process




- 5. Do not use the washing process.
- 6. Please refrain from using the product in environments specifically affected by excessive vibration, shock, dust, high humidity, gases, very high temperatures and very low temperatures such as outdoor equipment. It might cause degradation or destruction of the product. Even if it endures during a short time, long time quarification is not quaranteed.
- 7. For use of this product, be sure to put contact area of plug on position P(P4 full view) perpendicularly.
- 8. Plugs can be roughly classified to two types.
  - For mass production line automatic check (Press down type)
  - For manual check (With retentive lock): Unable to be used at production line.
- 9. When automatic inspections are to be performed during the manufacturing operations, request the MS-156 plug connector manual for examples of implementation.

### **▶** Packaging Specifications


#### ●Without vacuum cap



### ●With vacuum cap




#### ● Reel dimensions




Part Number	Reel Size	Packaging
MS-156HF	$R = \phi 380 mm$	10,000 pieces/reel
MS-156HF(20)	R = $\phi$ 180mm	2,000 pieces/reel

#### Reel dimensions



Part Number	Reel Size	Packaging
MS-156HF(02)	R = <i>\phi</i> 380mm	8,500 pieces/reel
MS-156HF(22)	$R = \phi 180 mm$	1,500 pieces/reel

### **●**Recommended Temperature Profile



#### Using Lead-free Solder paste

Maximum temperature	: 250℃
2 Peak temperature	: 240℃ to 250℃
3 Peak temperature time	: 10 sec. max.
<b>4</b> 230℃ min.	: 30 sec. max.
<b>5</b> 150℃ to 180℃	: 60 sec. to 90 sec.

Metal mask thickness Reflow cycles

: 0.1 to 0.12 mm : 2 cycles

### **■Plugs**

### ●Press down, right angle



### Simplified lock, right angle




### **■SMA Conversion Adapters**

### •Simplified lock, straight, short




### Simplified lock, straight, long






Part Number	CL No.	Durability
MS-156-C(LP)-1	358-0173-0	10,000 Times

Applicable cable: 1.5D-HQEW, 1.5D-QEW (Fujikura Ltd.)




Part Number	CL No.	Durability
MS-156-C(LP)-2	358-0174-3	500 Times

Applicable cable: 1.5D-HQEW, 1.5D-QEW (Fujikura Ltd.)



Part Number	CL No.	Durability
MS-156-HRMJ-2	358-0170-2	500 Times



Part Number	CL No.	Durability
MS-156-HRMJ-5	358-0177-1	500 Times

### ●Press down, with flange, short



#### ●Press down, with flange, long




# ●Press down, with flange (Increased self alignment)




### Floating







Part Number	CL No.	Durability
MS-156-HRMJ-3	358-0171-5	10,000 Times



Part Number	CL No.	Durability
MS-156-HRMJ-14	358-0198-1	10,000 Times



Part Number	CL No.	Durability
MS-156-HRMJ-6	358-0181-9	10,000 Times



Part Number	CL No.	Durability
MS-156-HRMJ-9	358-0180-6	10,000 Times

### ●Floating (Self-Pressing)



### ●Floating (Self-Pressing)




### ●Floating (Self-Pressing)




### Adapter for plug inspection







Part Number	CL No.	Durability
MS-156-HRMJ-10	358-0194-0	10,000 Times



Part Number	CL No.	Durability
MS-156-HRMJ-12	358-0196-6	10,000 Times




Part Number	CL No.	Durability
MS-156LP-HRMJ-4	358-0205-5	10,000 Times



Part Number	CL No.	Durability
MS-156R-HRMJ-1	358-0188-8	500 Times

### ●Adapter for plug inspection





Part Number	CL No.	Durability
MS-156R-NJ-1	358-0176-9	500 Times