



Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click to remove) Search Tips Within Results

Text Search: 'HSTTVA19-48-Q'

Your search criteria matched only one product, shown below

HSTTVA19-48-Q



Dual Wall Polyolefin DAMP-SHRINK™ Heat Shrink Tubing in 4 ft (1.2M) Pieces

- For damp locations
- Flexible tubing with an adhesive inner wall which seals and protects components from moisture and corrosion
- For use when a flexible adhesive lined tubing is needed
- Material Type: Polyolefin Cross -Linked with adhesive
- Shrink Ratio: 2:1
- Temperature Range: -67°F to 230°F (-55°C to 110°C)
- Flammability: Outer wall flame retardant
- Voltage Rating: 600V
- Mil Spec: AMSDTL-23053/4 Class 2

Part Number	HSTTVA19-48-Q
RoHS Compliancy Status	Compliant
Part Description	Dual Wall Adhesive Lined Thin Wall Heat Shrink (UL224 VWV)
Material	Polyolefin Cross-linked with adhesive
Color	Black
Military Specification	AMS-DTL-23053/4 Class 2
Length (ft.)	4
Length (m)	1.2
Flammability Rating	Outer Wall Flame Retardant
Max. Recovered I.D. (In.)	.093
Max. Recovered I.D. (mm)	2.4
Min. Expanded I.D. (In.)	.187
Min. Expanded I.D. (mm)	4.8
Nominal Diameter (In.)	.187
Nominal Diameter (mm)	4.8
Nominal Recovered Wall Thickness (In.)	.022
Nominal Recovered Wall Thickness (mm)	0.6
Pricing Description	Heat Shrink Thin, Adhesive, .19"(4.8mm) Dia
Shrink Ratio	2:1
Temperature Range	-67°F to 230°F
Min. Order UOM	PC
Min. Order Qty.	25
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.