

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

19

© COPYRIGHT 19

BY TE

ALL RIGHTS RESERVED.

PART LIST

(LISTA COMPONENTI)

ITEM (NO.)	DESCRIPTION (DESCRIZIONE)	DIMENSION (DIMENSIONE)	MATERIAL (MATERIALE)	QUANTITY REQUIRED PER ASSEMBLY (QUANTITA' RICHIESTA PER ASSEMBLATO)				
1	LEVER (LEVA)		PA 66GF30 COLOR GREEN (COLORE VERDE)	1	1	1	1	1
2	COVER (CORAZZA)	AL= 4,80 AR= 4,80	PA 66GF30 COLOR BLACK (COLORE NERO)	1				
3	COVER (CORAZZA)	AL= 8,00 AR= 8,00	PA 66GF30 COLOR GRAY (COLORE GRIGIO)		1			
4	COVER (CORAZZA)	AL=11,20 AR=11,20	PA 66GF30 COLOR BLUE (COLORE BLU)			1		
5	COVER (CORAZZA)	AL=11,20 AR= 4,80	PA 66GF30 COLOR WHITE (COLORE BIANCO)				1	
6	COVER (CORAZZA)	AL= 4,80 AR= 8,00	PA 66GF30 COLOR BROWN (COLORE MARRONE)					1
7	REC. HOUSING (ASSEM. BLOCCHETTO PORTA FEMMINE)			1				
	7_1	HOUSING (BLOCCHETTO)	PA 66GF13 COLOR BLACK (COLORE NERO)				1	
	7_2	SPRING (MOLLA DI C.C.)	STAINLESS STEEL (ACCIAIO INOX)				8	
8	REC. HOUSING (ASSEM. BLOCCHETTO PORTA FEMMINE)				1			
	8_1	HOUSING (BLOCCHETTO)	PA 66GF13 COLOR GRAY (COLORE GRIGIO)				1	
	8_2	SPRING (MOLLA DI C.C.)	STAINLESS STEEL (ACCIAIO INOX)				8	
9	REC. HOUSING (ASSEM. BLOCCHETTO PORTA FEMMINE)					1		
	9_1	HOUSING (BLOCCHETTO)	PA 66GF13 COLOR BLUE (COLORE BLU)				1	
	9_2	SPRING (MOLLA DI C.C.)	STAINLESS STEEL (ACCIAIO INOX)				8	
10	REC. HOUSING (ASSEM. BLOCCHETTO PORTA FEMMINE)						1	
	10_1	HOUSING (BLOCCHETTO)	PA 66GF13 COLOR WHITE (COLORE BIANCO)				1	
	10_2	SPRING (MOLLA DI C.C.)	STAINLESS STEEL (ACCIAIO INOX)				8	
11	REC. HOUSING (ASSEM. BLOCCHETTO PORTA FEMMINE)							1
	11_1	HOUSING (BLOCCHETTO)	PA 66GF13 COLOR BROWN (COLORE MARRONE)				1	
	11_2	SPRING (MOLLA DI C.C.)	STAINLESS STEEL (ACCIAIO INOX)				8	

284423-4 REV. A
BLACK (NERO)

284423-3 REV. A
GRAY (GRIGIO)

284423-6 REV. A
BLUE (BLU)

284423-7 REV. A
WHITE (BIANCO)

284423-5 REV. A
BROWN (MARRONE)

1

2

3

4

5

6

7

8

9

10

11

1

2

3

4

5

6

7

8

9

10

11

CLOSED LEVER (LEVA IN POSIZIONE CHIUSA)

OPENED LEVER (LEVA IN POSIZIONE APERTA)

21.2

10.5

SCALE 1:1

48.3

39.9±0.5

34

42.4

5.00

19.5±0.2

17.6±0.3

12.50

16.0

10.7

17.50

B

6.9

38.10

2.54

41.3±0.2

SCALE 3:1

NUMBER 32 CAVITIES SUITABLE ONLY FOR FEMALE CONNECTORS MQS P/N 144969-2
CuNiSi + STAINLESS STEEL SPRING GOLD PLATED ON CONTACT AREA
AND IN THE BACK OF THE SPRING. WIRE RANGE 0.35-0.5 mm²

(NUMERO 32 CAVITA' ADATTE SOLO PER CONTATTI FEMMINA MQS P.N. 144969-2
CuNiSi + MOLLA ACCIAIO INOX DORATA NELLA ZONA DI CONTATTO
E SUL DORSO DELLA MOLLA. RANGO FILO 0.35-0.5 mm²)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN P. CASSANDRIN 290CT1999

CHK -

APVD A. GENIA 290CT1999

PRODUCT SPEC 108-20223

APPLICATION SPEC 114-15077

WEIGHT -

CUSTOMER DRAWING

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.3

1 PLC ±0.2

2 PLC ±0.1

3 PLC ±

4 PLC ±

ANGLES ±°

MATERIAL SEE TABLE (VEDI TABELLA)

FINISH SEE TABLE (VEDI TABELLA)

NAME K1Y ASS'Y FOR 32 POSITIONS AIRBAG CONNECTOR

SIZE A2

CAGE CODE -

DRAWING NO C=284423

RESTRICTED TO -

SCALE 2:1

SHEET 1 OF 1

REV A5

1471-9 (3/13)