

PRODUCT NUMBER

20020012-XXXXXXLF

20020012-

PITCH

C: 3.50mm
D: 3.81mm
G: 5.00mm
H: 5.08mm

POLES

02: 2 POLES
03: 3 POLES
04: 4 POLES
24: 24 POLES

LF : DENOTED RoHS COMPATIBLE

1 : STANDARD PRODUCT
W/ BOX PACKING

SCREW CODE

CODE	SCREW TYPE	AVAILABILITY
A	-/+	ON REQUEST ONLY
B	-	STANDARD

ALL FLANGE SCREWS ARE ONLY AVAILABLE IN +/-
COMBINATION SCREW TYPES.

HOUSING CODE

CODE	COLOR	AVAILABILITY
1	GREEN(RAL 6018/T)	STANDARD
2	BLACK	ON REQUEST ONLY
3	GREY(RAL 7004/P)	ON REQUEST ONLY
4	BLUE(RAL 5015/A)	ON REQUEST ONLY

PROPERTY TABLE

FCI SERIES NAME		03-350	03-381	03-500	03-508	
PITCH (mm)		3.50	3.81	5.00	5.08	
VOLTAGE RATING (VAC)		300	300	300	300	
CURRENT RATING (A)		10	10	10	10	
APPLICABLE WIRE RANGE (AWG)		1-WIRE	16~28	16~28	12~22	12~22
		2-WIRE	20	20	18	18
WIRE CROSS SECTION (mm ²)	SOLID	1-WIRE	1.5	1.5	2.5	2.5
		2-WIRE	0.5	0.5	1.0	1.0
	STRANDED	1-WIRE	1.5	1.5	2.5	2.5
		2-WIRE	0.75	0.75	1.5	1.5
OPENING CONTACT HOUSING(mm ²)		1.8x2.4	1.8x2.4	2.6x2.8	2.6x2.8	
WIRE STRIP LENGTH(mm)		6~7	6~7	6~7	6~7	
TORQUE +/– 10% (N-m/Lb-in)		0.19/1.7	0.19/1.7	0.4/3.5	0.4/3.5	
SCREW		M2x0.4	M2x0.4	M2.5x0.4	M2.5x0.4	
WITHSTANDING VOLTAGE (kV)		1.6	1.6	1.6	1.6	
OPERATING TEMP. (°C)		–40~+115	–40~+115	–40~+115	–40~+115	
POLES AVAILABLE		02~24	02~24	02~24	02~24	

SAFETY CERTIFICATE



NOTES:

1. MATERIALS

- 1-1 HOUSING: THERMALPLASTIC RESIN, UL 94V-0 RATED.
1-2 SCREW: STEEL, ZINC PLATED.
1-3 CLAMP: COPPER ALLOY, NICKEL PLATED.
1-4 TERMINAL: COPPER ALLOY, TIN PLATED.

2. PRODUCT SPECIFICATION REFER TO FCI GS-12-625.


3. PRODUCT PACKING SPECIFICATION REFER TO FCI GS-14-1394.

4. FCI, SAFETY CERTIFICATE LOGO AND SERIES NAME TO BE SHOWN ON PRODUCT SURFACE.

5. THE PRODUCTS WHERE THE PART NUMBER END IN "LF" MEET THE EUROPEAN UNION DIRECTIVE AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.

mat'l. code				surface ASME Y14.5				tolerance ASME Y14.5				projection 		product family TERMINAL BLOCK																																					
litr				ecn no				dr				date				tolerances unless otherwise specified				title																															
A				T10-0082				WL				080810				angles				X.±0.5		MM [INCH]		TERMINAL BLOCK PLUGGABLE, PLUG, SIGNAL, W/FLANGE FRONT SCREW																											
B				T10-0158				WL				100410				X.X±0.3																																			
C				T10-0180				WL				111510				X'±1"				X.XX±0.1		scale		sheet 1 of 5																											
D				T10-0186				WL				120810				dr				WENDY CHEN				051810				FCI 		20020012				A4																	
E				T11-0006				WL				012611				enr				JASON HSU				051810																											
F				T-005908				WL				091311				chr				GARY HSIEH				051810																											
																appd				JOSEPH HSIA				051810				type		CUSTOMER Drawing																					
sheet index				revision				F				F				F				F				F																											
				sheet				1				2				3				4				5																											

PRODUCT NUMBER	SERIES NAME	PITCH
20020012-CXXXXXXLF	03-350	3.50 mm




N = Number of poles

Dim A = $N \times 3.5 [0.138] + 0.80 [0.031]$ Dim B = $(N-1) \times 3.5 [0.138]$ Dim C = $(N-1) \times 3.5 [0.138] + 8.6 [0.339]$

Poles	Dim A	Dim B	Dim C
2-4p	$\pm 0.10 [0.004]$	$\pm 0.15 [0.006]$	
5-7p	$\pm 0.15 [0.006]$	$\pm 0.20 [0.008]$	
8-12p	$\pm 0.20 [0.008]$	$\pm 0.25 [0.010]$	
13-18p	$\pm 0.25 [0.010]$	$\pm 0.30 [0.012]$	
19-24p	$\pm 0.30 [0.012]$	$\pm 0.40 [0.016]$	




mat'l. code	surface ASME Y14.5	tolerance ASME Y14.5	projection	product family TERMINAL BLOCK
ltr	ecn no	dr	date	title
F				TERMINAL BLOCK PLUGGABLE, PLUG, SIGNAL, W/FLANGE FRONT SCREW
				sheet 2 of 5 size
				20020012 A4
				type CUSTOMER Drawing
sheet index	revision sheet			

PRODUCT NUMBER	SERIES NAME	PITCH
20020012-DXXXXXLf	03-381	3.81 mm




N = Number of poles
 Dim A = $N \times 3.81 [.150] + 0.80 [.031]$
 Dim B = $(N-1) \times 3.81 [.150]$
 Dim C = $N \times 3.81 [.150] + 9.6 [.378]$
 Dim D = $(N-1) \times 3.81 [.150] + 9.0 [.354]$

Poles	Tolerance
2-6p	$\pm 0.15 [.006]$
7-11p	$\pm 0.20 [.008]$
12-17p	$\pm 0.25 [.010]$
18-24p	$\pm 0.30 [.012]$






mat'l. code	surface ASME Y14.5 ✓	tolerance ASME Y14.5	projection MM [INCH]	product family TERMINAL BLOCK
ltr	ecn no	dr	date	title TERMINAL BLOCK PLUGGABLE, PLUG, SIGNAL, W/FLANGE FRONT SCREW
F				dwg no 20020012
				sheet 3 of 5
				size A4
				type CUSTOMER Drawing
sheet index	revision sheet			

PRODUCT NUMBER	SERIES NAME	PITCH
20020012-GXXXXXL	03-500	5.00 mm






N = Number of poles
 Dim A = $N \times 5.0 [.197] + 0.5 [.020]$
 Dim B = $(N-1) \times 5.0 [.197]$
 Dim C = $N \times 5.0 [.197]$
 Dim D = $(N+1) \times 5.0 [.197]$
 Dim E = $(N+2) \times 5.0 [.197]$

Poles	Tolerance
2-7p	$\pm 0.15 [.006]$
8-12p	$\pm 0.25 [.010]$
13-18p	$\pm 0.30 [.012]$
19-24p	$\pm 0.40 [.016]$



mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family TERMINAL BLOCK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
F				angles	X.±0.5	MM	TERMINAL BLOCK
				linear	X.X±0.3	[INCH]	PLUGGABLE, PLUG, SIGNAL, W/FLANGE
				X*±1*	X.XX±0.1	scale	FRONT SCREW
		dr	WENDY CHEN	051810		FCI	sheet 4 of 5
		enr	JASON HSU	051810			size
		chr	GARY HSIEH	051810			20020012
		appd	JOSEPH HSIA	051810			A4
sheet index	revision sheet					type	CUSTOMER Drawing


PRODUCT NUMBER	SERIES NAME	PITCH
20020012-HXXXXXXLF	03-508	5.08 mm



SECTION P-P

N = Number of poles
 Dim A = $N \times 5.08 [.200] + 0.50 [.020]$
 Dim B = $(N-1) \times 5.08 [.200]$
 Dim C = $N \times 5.08 [.200]$
 Dim D = $(N+1) \times 5.08 [.200]$
 Dim E = $(N+2) \times 5.08 [.200]$

Poles	Tolerance
2-6p	$\pm 0.15 [.006]$
7-12p	$\pm 0.25 [.010]$
13-18p	$\pm 0.30 [.012]$
19-24p	$\pm 0.40 [.016]$



mat'l. code				surface ASME Y14.5 ✓	tolerance ASME Y14.5	projection MM INCH	product family TERMINAL BLOCK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
F				angles	X.±0.5 X.X±0.3 X.XX±0.1	scale	TERMINAL BLOCK PLUGGABLE, PLUG, SIGNAL, W/FLANGE FRONT SCREW
		dr	WENDY CHEN	051810			sheet 5 of 5 size
		enr	JASON HSU	051810			20020012 A4
		chr	GARY HSIEH	051810			
		appd	JOSEPH HSIA	051810			
sheet index	revision sheet						type CUSTOMER Drawing