


Part Number: THT-46-497-10

Thermal Transfer Printable Labels

Printable, low-profile polyimide labels for thermal transfer printers. Please Note: This material is UL recognized with its respective ribbon.



Specifications:

Size: 0.750" W x 0.250" H (19.05 mm W x 6.35 mm H)

Printable Area: 0.750" W x 0.250" H (19.05 mm W x 6.35 mm H)

Label Type/Style: Label

Color: White

Finish: Matte

Material Type: Polyimide

Material Description: Low-Profile Polyimide

Adhesive: Permanent Acrylic

Agency Approval(s)/Compliance: UL Recognized

Special Properties: Excellent resistance to harsh fluxing and wave solder environments, Low profile, Resists all commonly employed methods of cleaning

Vertical Repeat: 0.350" (8.89 mm)

Web Width: 3.350" (85.09 mm)

Application(s): Circuit Board & Component ID, SMT - Top/Bottom, Through Hole - Bottom, Through Hole - Top

Through Hole Technology: Top: Yes, Bottom: Yes

Surface Mount Technology: Yes, this material will work with this application

After Process: Yes, this material will work with this application

Recommended Ribbon Series: 6000

Acceptable Ribbon Series: 4800

Printer Compatibility: Brady 1244, Brady 1344, Brady 200MVP Plus, Brady 2461, Brady 300MVP Plus, Brady 300X-Plus II, Brady 3481, Brady 360X-Plus II, Brady 600X-Plus II, Brady 6441, Brady BBP312, Tagus™ T200, Tagus™ T300, Thermal Transfer Printers

RoHS Compatibility: Compliant with RoHS Directive.