

## 1-1825143-9 Product Details



1-1825143-9

### Toggle Switches


[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- AE Series
- Double Pole - Double Throw Configuration (Pole-Throw)
- Current Rating = 0.4 VA A
- Mount Style = Through-Hole
- Termination Type = Printed Circuit

[View all Features](#)

TE Internal Number: 1-1825143-9



Active

[Add to My Part List](#)

[Request Sample](#)

[Find Similar Products](#)

[Buy Product](#)

### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [GEMINI AE SERIES TOGGLE SWITCH, DOUBLE POLE](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- [SWITCHES CORE PROGRAM CATALOG](#) (PDF, English)
- [GEMINI SERIES SWITCHES QUICK REF GUIDE 2-1773458-5](#) (PDF, English)

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Additional Product Images:

- [Product Photo](#)
- [Dimensional Drawing](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Series = AE
- Configuration (Pole-Throw) = Double Pole - Double Throw
- Termination Type = Printed Circuit

#### Electrical Characteristics:

- Current Rating (A) = 0.4 VA

#### Termination Features:

- Seal Type = Terminal Seal (epoxy)

#### Body Features:

- Mount Style = Through-Hole

#### Contact Features:

- Contact Plating = Gold

#### Housing Features:

- Toggle Style = Baton Long
- Toggle Length (mm [in]) = 12.70 [0.500]
- Process Sealed = Yes
- Bushing Style = Unthreaded
- Bushing Type = Plain
- UL Flammability Rating = UL 94V-0

#### Configuration Features:

- [Operating Function](#) = On Off On

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant
- [UL Rating](#) = Contact Only

#### Other:

- Brand = Alcoswitch
- Comment = Process seal meets MIL-STD-202, Method 112 test cond. A & D at 85°C.

### Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

### Quick Links

[Check Distributor Inventory](#)
[Cross Reference Products](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

### Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage Your Account](#)

### Keep Me Informed

Receive TE News, Events &amp; Technology Updates

Enter your email address

