



Product: [6540FT](#)

Thermostat & Control, #22-2c, TC, O/A Foil, CMP

Product Description

Thermostat & Control Cable, Plenum-CMP, 1-22 AWG stranded tinned copper pair with foam FEP insulation, Beldfoil® shield, Flamarrest® jacket

Technical Specifications

Product Overview

Suitable Applications:	Thermostat, Control, Noisy Environment
------------------------	--

Physical Characteristics (Overall)

Conductor			
AWG	Stranding	Material	No. of Pairs
22	7x30	TC - Tinned Copper	1
Conductor Count:			2

Insulation	
Material	
FEP - Fluorinated Ethylene Propylene (Foam)	

Color Chart	
Number	Color
1	Black & White

Outer Shield Material						
Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Alum / Poly	Beldfoil®	100%	TC - Tinned Copper	22	Solid

Outer Jacket Material		
Material	Material Trade Name	Nominal Diameter
PVC-LS - Polyvinyl Chloride (Low Smoke)	Flamarrest®	0.162 in

Electrical Characteristics

Conductor DCR	
Nominal Conductor DCR	Nominal Outer Shield DCR
14.5 Ohm/1000ft	19 Ohm/1000ft

Capacitance	
Nom. Capacitance Conductor to Conductor	
16.9 pF/ft	

Inductance	
Nominal Inductance	
0.21 µH/ft	

Delay

Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]
78 ns/100m	78%

High Freq

Max./Min. Input Impedance (unFitted)
100 ± 22 Ohm

Current

Max. Recommended Current [A]
4.3 Amps per Conductor at 20°C

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

UL Temp Rating:	75°C
Operating Temp Range:	-20°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	13 lbs/1000ft
Max. Pull Tension:	27 lbs
Min Bend Radius/Minor Axis:	1.6 in

Standards

NEC/(UL) Compliance:	CMP
CEC/C(UL) Compliance:	CMP

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2006-02-01
MII Order #39 (China RoHS):	Yes

Flammability, LS0H, Toxicity Testing

C(UL) Flammability:	FT6
UL Flammability:	NFPA 262 Plenum Flame Test (UL910)
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

Part Number

Variants

Item #	Color	UPC
6540FT 0011000	Brown	612825178217

History

Update and Revision:	Revision Number: 0.244 Revision Date: 06-08-2020
----------------------	--

© 2020 Belden, Inc  
All Rights Reserved.  
Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.  
Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.  
All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.