

## DETAILS

Product Number	CN13113_LENINA-S-DL
Family	Lenina
Type	RefPack
Color	metal
Diameter	74 mm
Height	46.4 mm
Style	round
Optic Material	PC
Holder Material	PC
Fastening	socket, screw, socket
Status	ready
ROHS Compliant	Yes
Date Updated	30/10/2012



## OPTICAL PROPERTIES




LED	Viewing Angle	Light Beam	Efficiency	cd/lm	connector
Soleriq E30	26 degrees		82 %	2.200	-

D

C

B

A



#### NOTE:

Using optional sublens, add 2.1mm to the system height

Dimension 'h2' varies from 4.5mm to 7mm depending on the LED specific base part

This drawing is our property.  
It can't be reproduced  
or communicated without  
our written agreement.



Ledil Oy  
Salorankatu 10  
FIN-24240 SALO  
Finland

DRAWING TITLE


Datasheet Lenina series

DRAWN BY ks	DATE 23.04.2014	SIZE A4	DRAWING NUMBER	REV --
CHECKED BY	DATE			
DESIGNED BY pl	DATE 08.03.2012	SCALE 1:1	WEIGHT(g)	SHEET 1/1


D

A

Luminaire: LEDiL Oy CN13113\_LENINA-S-DL\_(SoleriqE30) Eff.82.0%  
Lamps: 1 x Osram Soleriq E30 (1262.22lm@250mA)



Luminaire: LEDiL Oy CN13113\_LENINA-S-DL\_(SoleriqE30) Eff.82.0%  
Lamps: 1 x Osram Soleriq E30 (1262.22lm@250mA)



**NOTE: The typical divergence will be changed by different color, chip size and chip position tolerance. The typical total divergence is the full angle measured where the luminous intensity is half of the peak value.**

## **GENERAL INFORMATION**

- Product series especially designed & optimized for series of LEDs.
- Special care taken to make light distribution as uniform as possible.
- Reflector is made of aluminium coated PC (120 degrees of Celcius / 248 degrees of Fahrenheit) with protective lacquer (short term 100 degrees of Celcius / 212 degrees of Fahrenheit).

Note! Due to use of high power COB's with this product, special attention to proper thermal design is highly recommended. LEDiL has no liability for direct, indirect or consecutive damages arising from the LEDiL products being used outside of the recommended temperature range.