





A

1. $0.76\mu\text{m}$ [.000030] MIN PRECIOUS METAL PLATE ON MATING END FOR A LENGTH OF 5.08 [.200] MIN WITH $1.27\mu\text{m}$ [.000050] MIN MATTE TIN PLATE IN WIRE CRIMP AREA, BOTH OVER $1.27\mu\text{m}$ [.000050] MIN NICKEL PLATE. CONFORMS TO THE REQUIREMENTS OF TE CONNECTIVITY PRODUCT SPEC 108-10042, BASED ON EIA/ECA-364-1000.01A (CONTROLLED ENVIRONMENT APPLICATIONS).
2. REELED FOR MINI-APPLICATOR.
3. GOLD PLATING NEED NOT APPEAR IN THIS AREA.
4. $0.76\mu\text{m}$ [.000030] MIN PRECIOUS METAL PLATE ON MATING END FOR A LENGTH OF 5.08 [.200] MIN WITH A UNIFORM GRADIENT TO $0.25\mu\text{m}$ [.000010] ON REMAINDER, OVER $1.27\mu\text{m}$ [.000050] MIN NICKEL PLATE. GOLD FLASH ALL OVER. CONFORMS TO THE REQUIREMENTS OF TE CONNECTIVITY PRODUCT SPEC 108-10042, BASED ON EIA/ECA-364-1000.01A (CONTROLLED ENVIRONMENT APPLICATIONS).
5. $0.38\mu\text{m}$ [.000015] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [.200] MIN WITH $1.27\mu\text{m}$ [.000050] MIN MATTE TIN PLATE IN WIRE CRIMP AREA, BOTH OVER $1.27\mu\text{m}$ [.000050] NICKEL PER QQ-N-290.
6. WIRE RANGE 26-30 AWG.
7. INSULATION RANGE 1.02 [.040]-1.52 [.060] DIA.
8. $1.27\mu\text{m}$ [.000050] MIN TIN-LEAD PER MIL-T-10727 OVER
 $1.27\mu\text{m}$ [.000050] MIN NICKEL PER QQ-N-290.
9. $0.38\mu\text{m}$ [.000015] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [.200] MIN, 1.27 MIL-T-10727 FOR A LENGTH OF 5.69 [.224] MIN ON OPPOSITE END, BOTH OVER $1.27\mu\text{m}$ [.000050] MIN NICKEL PER QQ-N-290 ON ENTIRE CONTACT.
10. $1.27\mu\text{m}$ [.000050] MIN TIN PER MIL-T-10727 OVER
 $1.27\mu\text{m}$ [.000050] MIN NICKEL PER QQ-N-290.

			—	1—66425—2
OBSOLETE			66429—6	1—66425—1
			66429—4	66425—8
			66429—3	66425—7
OBSOLETE			—	66425—6
OBSOLETE			66429—1	66425—5
	STANDARD		66429—4	66425—4
	STANDARD		66429—3	66425—3
OBSOLETE	STANDARD		66429—1	66425—1
	REELING	PIN BODY FINISH	LOOSE PIECE REF	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN V. FURLER 28JUL03 CHK G. STEINHAUER 28JUL03 APVD G. STEINHAUER 28JUL03		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME PIN ASSEMBLY, .062, TYPE III+	
		0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 [.005] 3 PLC ± - 4 PLC ± - ANGLES ± -			
MATERIAL SEE CALLOUTS		FINISH SEE TABLE			
		WEIGHT -			
CUSTOMER DRAWING				SIZE A2	CAGE CODE 00779
				DRAWING NO G=66425	RESTRICTED TO -
				SCALE 8:1	SHEET 1 of 1
				REV V	