



Search Results

- Evaluate
- [FAQ's](#)
- How to Buy
- [Bill of Material](#)
 - [Favorite Products List](#)
 - [Locate Distributor](#)

[Home](#) > [Products Overview](#) > [Search Results](#) >

Current refinements (click to remove) [Search Tips](#)

Text Search: 'HSTTV12-48-Q'

Your search criteria matched only one product, shown below

HSTTV12-48-Q



- Shrink ratio of 2:1 insulates a wide range of diameters and irregular shapes
 - Cross -linked, UV resistant material improves flame retardancy, chemical, and temperature resistance
 - Available in various colors for permanent, cost effective color coding
- Meets Mil Spec AMSDTL-23053/5 Class 3.

	Part Number	HSTTV12-48-Q
	RoHS Compliancy Status	Compliant
	Part Description	Thin Wall Polyolefin Heat Shrink (UL224 VW1)
	Material	Highly flame retardant polyolefin cross-linked^^
	Color	Black
	CSA Certified	Yes
	Military Specification	AMS-DTL-23053/5 Class 3
	UL Recognized	E122770
	Length (ft.)	4
	Length (m)	1.2
	CE Compliant	No
	CE Marking	No
	Flammability Rating	UL224 VW-1
	Max. Recovered I.D. (In.)	.062
	Max. Recovered I.D. (mm)	1.6
	Min. Expanded I.D. (In.)	.125
	Min. Expanded I.D. (mm)	3.2
	Nominal Diameter (In.)	.125
	Nominal Diameter (mm)	3.2
	Nominal Recovered Wall Thickness (In.)	.020
	Nominal Recovered Wall Thickness (mm)	0.5
	Pricing Description	Heat Shrink Thin VW1, .12"(3.2mm) Dia, Black
	Shrink Ratio	2:1
	Temperature Range	-67°F to 257°F (-55°C to 125°C)
	Min. Order UOM	PC
	Min. Order Qty.	25
	BOM Qty. (# of Pkgs.)	0
	Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.