


Messleitungen / measuring leads

MVL S WS 100/1



Produktbeschreibung	Product description		
Beschreibung	Description	Berührungssichere Messleitung nach IEC 61010, beidseitig Sicherheitsstecker mit 2 mm Ø sowie 2 mm Buchse für Turmsteckbauweise. Kontaktfeder Kupfer-Beryllium vergoldet. Hochflexible, doppelt isolierte Litzenleitung, mit trittfesten Griffhülsen. Eingearbeiteter Farbindikator zur Erkennung von Schäden an der Leitungsisolation.	Safety measuring lead according to IEC 61010, with 2 mm Ø safety plugs on both sides and 2 mm sockets for onward connection capability. Gold-plated copper beryllium contact spring. Highly flexible, double insulated stranded lead and shatter-proof grip sleeves. Built in colour indicator for easy identification of insulation damages.
Typ	Type	MVL S WS 100/1	MVL S WS 100/1
Leitungslänge	Cable length	100 cm	100 cm
Leitungsquerschnitt	Conductor size	1 mm ²	1 mm ²
Gehäusefarbe / Artikel-Nr.	Housing color / article-no.	● 975 696-700 ● 975 696-701 ● 975 696-702 ● 975 696-703 ● 975 696-704 ● 975 696-705 ● 975 696-706 ● 975 696-707 ● 975 696-709	
Zeichnung	Drawing		
Technische Daten	Technical data		
Stiftdurchmesser	Pin dimensions	2 mm	2 mm
Kontaktart	Type of contact	gefederter Stift	spring-loaded pin
Leitungstyp	Cable type	LEH-XY	LEH-XY
Leitungsspezifikation	Cable specification	hochflexible Schlauchleitung	highly flexible lead
Litzenaufbau	Wire stranding	259 x 0,07 mm	259 x 0.07 mm
Bemessungsspannung	Rated voltage	AC/DC 1000V	AC/DC 1000V
Messkategorie lt. IEC61010	Measurement cat. acc. to IEC61010	CAT III	CAT III
Bemessungsstrom (Derating Kurve beachten)	Rated current (consider derating curve)	10 A	10 A
Durchgangswiderstand	Contact resistance	24 mOhm	24 mOhm
Werkstoff	Material		
Kontaktmaterial	Contact material	Kontaktstift: Messing Kontaktfeder: Kupfer-Beryllium	contact pin: brass contact spring: copper-beryllium
Kontaktflächenmaterial	Contact surface material	Gold	gold
Gehäusematerial	Housing material	PA	PA
Leitungsmaterial	Cable material	PVC	PVC
Umgebungsbedingungen	Environmental conditions		
Temperaturbereich	Temperature range	-15°C bis +70°C	-15°C to +70°C
Brennbarkeitsklassen	Inflammability class		
Gehäuse (Grundmaterial)	Housing (basic material)	UL 94 V-2	UL 94 V-2