

10mm BAYONET BASED LED LAMP


XYSG101W6V



SUN LED

Email : sales@us.sunled.com

Web Site : www.sunled.com



Notes:


1. All dimensions are in millimeters (inches).
2. Tolerance is $\pm 0.25(0.01)$ unless otherwise noted.

Absolute maximum ratings ($T_A=25^{\circ}\text{C}$)		SG (InGaAlP)	Unit
Reverse voltage	V_R	5	V
Forward voltage	V_F	7	V
Power dissipation	P_T	150	mW
Operating temperature	T_A	-40 ~ +70	$^{\circ}\text{C}$
Storage temperature	T_{stg}	-40 ~ +85	

Operating Characteristics ($T_A=25^{\circ}\text{C}$)		SG (InGaAlP)	Unit
Forward current (typ.) ($V_F=6\text{V}$)	I_F	23	mA
Reverse current ($V_R=5\text{V}$)	I_R	10	μA
Wavelength at peak emission ($V_F=6\text{V}$)	λ_{peak}	574	nm
Wavelength at Dominant emission ($V_F=6\text{V}$)	λ_D	568	nm
Spectral Line half-width ($V_F=6\text{V}$)	$\Delta\lambda$	26	nm

Part Number	Emitting Color	Emitting Material	Lens-color	Luminous Intensity ($V=6\text{V}$) mcd		Wavelength nm λ_P	Viewing Angle $2\theta_{1/2}$
				min.	typ.		
XYSG101W6V	Green	InGaAlP	Water Clear	400	890	574	20°

XYSG101W6V



◆SG

