

MATERIAL AND FINISH

Insulator: Polycarbonate,
UL-94V-0 rated
Contacts: Brass, Nickel plated

ELECTRICAL SPECIFICATIONS:

Current rating: 10 A
Voltage rating: 250 VAC
Insulation resistance: 100 Mohm
min. at 500 VDC
Dielectric withstanding voltage:
2000 VAC for one minute

ORDERING CODE:

42R39-3 $\frac{5}{1}$ $\frac{2}{2}$ $\frac{3}{3}$

- 1) COLOR
1 = BLACK
2 = GRAY

- 2) ELECTRICAL CIRCUIT
CONFIGURATION

3 = 10A 250V 70°C
2+GROUND, 1 FUSE
2 POLE SWITCH

4 = 10A 250V 70°C
2+GROUND, 2 FUSE
2 POLE SWITCH


7 = 10A 250V 120°C
2+GROUND, 1 FUSE
2 POLE SWITCH

8 = 10A 250V 120°C
2+GROUND, 2 FUSE
2 POLE SWITCH






11 = 10A 250V 70°C
2 POLE, 1 FUSE
2 POLE SWITCH

12 = 10A 250V 70°C
2 POLE, 2 FUSE
2 POLE SWITCH

- 3) PANEL THICKNESS



RECOMMENDED
PANEL
CUTOUT



SCHEMATICS

REV	REVISIONS		DATE	CHANGE	CHK	CHK	APPR
	NO.	DESCRIPTION					

P/N	A	MAX. PANEL THICKNESS
42R39-3X5X-150	1.5	1.5
42R39-3X5X-200	2.0	2.0
ADDITIONAL PANEL THICKNESS, ONE POLE SWITCH, AND .187 QC TERMINALS AVAILABLE ON REQUEST		

TOLERANCE UNLESS OTHERWISE SPECIFIED			
X	±	1	
X.X	±	0.4	
X.XX	±	0.20	
DRAWN BY	GQ	DATE:	09/24/01
CHECK BY	TD	DATE:	09/26/01
APPR BY	PB	DATE:	09/26/01

Power Dynamics, Inc.

Phone: 973 560-0019 Whippany, New Jersey Fax: 973 560-0076

PART: 1EC 60320 APPL. INLET, VOLTAGE SELECTOR
FUSE HOLDER; QC TERMINALS; SNAP-IN

PART #:	42R39-3X5X-XXX	SHEET	1 of 1
SIZE:	A	ALL DIMENSIONS FOR REFERENCE ONLY DIMENSIONS ARE IN MILLIMETERS	
SCALE:	NTS		
REV:			