

## Honeywell Sensing and Control



Home > Products > Stainless Steel Media Isolated > Eclipse > Product Page

### EC500PS1HC



**Eclipse Series Stainless Steel Pressure Sensor, Amplified Output, Sealed Gage, 0 psi to 500 psi, Item Number 9251704**

*Actual product appearance may vary.*

#### Features

- Voltage or current output
- 15 PSIG through 7100 PSIS ranges
- CE versions available
- High performance at low price
- Weatherproof type connector
- Reverse-polarity protection
- Low-excitation voltage
- Flexibility for the designer
- Suitable for many applications
- Ready for Europe
- Reduces OEM system cost
- High reliability and user flexibility
- Not damaged by reversed wiring
- Suitable for ORV or marine use
- Complete environmental protection for electronics

#### Potential Applications

- Energy management: "smart" compressors, refrigeration/ chiller control
- Hydraulic / pneumatic controls
- Automotive air compressors
- Off road vehicles

#### Description

The Eclipse is designed for high-volume OEM's needing a lowcost pressure transmitter for industrial or other heavy-duty applications. The Eclipse's combination of rugged packaging, internal signal amplification and price make it ideal for many applications.

The pressure media is contained by a brazed assembly of stainless steel. There are no hidden O-rings or elastomers containing the media. A plated steel case protects the internal electronics.

It is available with either a 0.5 Volt to 4.5 volt or 4 mA to 20 mA output. The 4 mA to 20 mA output is useful for applications where electrical noise may be a concern. Units with the Hirschmann connectors are CE approved.

#### Supporting Documentation

[Dimensions and Circuity](#)

[Documentation](#)

#### My Links

[Login to iCOM](#)  
[Login as Rep/AD](#)  
[Login as Guest](#)  
[Login to Digital University](#)

#### Keyword Search

Search for product and support information.

#### Product Search

Part number search:

Use (\*) to expand search

#### Specification Search

Product Specifications	
Measurement Type	Sealed Gage
Signal Conditioning	Amplified
Pressure Range	0 psi to 500 psi
Supply Voltage	5.0 Vdc $\pm$ 0.25 Vdc
Maximum Overpressure	750 psi
Burst Pressure	2,500 psi
Port Style	1/8 - 27 NPT
Temperature Compensation	Yes
Output Type	0.5 Vdc to 4.5 Vdc
Protection Circuitry	Reverse Polarity
Accuracy	0.25% full scale BFSL
Response Time	less than 1.0 ms
Insulation Resistance	1000 Mohms @ 50 Vdc max.
Output Calibration	Yes
Termination Type	Hirschmann Connector
Weight	85 grams [3.0 ounces]
Full Scale Span	4 Vdc
Operating Temperature Range	-40 °C to 105 °C [ -40 °F to 221 °F ]
Compensated Temperature Range	-1 °C to 82 °C [30 °F to 180 °F]
Storage Temperature Range	NO IDEA SHARED FORMULA EXP PTG
Media Compatibility	Limited only to those media which will not attack a brazed assembly of 300 Series stainless steel parts
Approvals	CE, ULc, AGA, CSA
UNSPSC Code	411121
UNSPSC Commodity	Transducers
Availability	Global
Series Name	Eclipse

Product Specifications	
Measurement Type	Sealed Gage
Signal Conditioning	Amplified
Pressure Range	0 psi to 500 psi
Supply Voltage	5.0 Vdc $\pm$ 0.25 Vdc
Maximum Overpressure	750 psi
Burst Pressure	2,500 psi
Port Style	1/8 - 27 NPT
Temperature Compensation	Yes
Output Type	0.5 Vdc to 4.5 Vdc
Protection Circuitry	Reverse Polarity
Accuracy	0.25% full scale BFSL
Response Time	less than 1.0 ms
Insulation Resistance	1000 Mohms @ 50 Vdc max.
Output Calibration	Yes
Termination Type	Hirschmann Connector
Weight	85 grams [3.0 ounces]
Full Scale Span	4 Vdc
Operating Temperature Range	-40 °C to 105 °C [ -40 °F to 221 °F ]
Compensated Temperature Range	-1 °C to 82 °C [30 °F to 180 °F]
Storage Temperature Range	NO IDEA SHARED FORMULA EXP PTG
Media Compatibility	Limited only to those media which will not attack a brazed assembly of 300 Series stainless steel parts
Approvals	CE, ULc, AGA, CSA
UNSPSC Code	411121
UNSPSC Commodity	Transducers
Availability	Global
Series Name	Eclipse