



REV	DESCRIPTION	DATE
D	EXTENSION 124360 WAS 123108.	10-31-94
E	O-RING 507166 WAS 500787.	04-23-96
F	FILE OBSOLETE	11-26-96

NOTES:

- 1 FOR USE WITH 225, 245, 226, 246, 247, 2502 & 4802 TOOLS,
USE WITH ADAPTOR P/N 121395.
- 2 TORQUE ALL THREADED JOINTS TO 28-32 FT/LBS
- ⚠ TORQUE TO 3-5 FT/LBS
- ⚠ ANVIL ASSEMBLY 124107 CONSISTS OF:
124106 ANVIL
124105 RATCHET PIN (2)
- ⓔ 507166 O-RING



FILE OBSOLETE	
OBSOLESCE	DATE: 11/26/96
OBSOLETE	DATE: 11/26/96
SUPERSEDED BY:	99-3465



FORM: KE104 REV C		By accepting this proprietary Huck drawing, recipient agrees not to reproduce or disclose any part thereof to any others without the written permission of Huck International, Inc.				
MATERIAL:	-	SPEC:	TOLERANCES UNLESS OTHERWISE SPECIFIED: (ALL DIMENSIONS ARE IN INCHES)		HUCK INTERNATIONAL, INC., I.S.D. 85 GRAND STREET, P.O. BOX 2270 KINGSTON, NEW YORK 12401	
HARDNESS:	-	(RAW OR STOCKED STATE)				
HEAT TREAT TO:	-	SPEC:	.XX, .XXX ±	NOSE ASSEMBLY -12 LP HUCKTAINER		
SURFACE TREAT:	-	SPEC:	INT. COR. RADII			
SURFACE FINISH NOT TO EXCEED: Ra			BREAK EDGES		DET: T.L. CK:	DATE: 01-12-93 SCALE: 2/1
IDENTIFICATION PER SPEC 42-311: ★ ETCH			ANGLES ±		FOC.	B 99-3433
SURFACES TO BE ☉, //, ⊕, ⊥, & ▽ WITHIN T.I.R.			FINAL ASSY:		FAC.	