

TABLE I				
DASH NO	A INSIDE DIA		B OUTSIDE DIA	
	MIN	MAX	MIN	MAX
09	.24 (6.1)	.28 (7.1)	.38 (9.7)	.42 (10.7)
12	.33 (8.4)	.37 (9.4)	.48 (12.2)	.52 (13.2)
14	.40 (10.2)	.44 (11.2)	.55 (13.9)	.59 (15.0)
16	.45 (11.4)	.50 (12.7)	.60 (15.2)	.66 (16.8)
20	.57 (14.5)	.62 (15.7)	.71 (18.0)	.77 (19.5)
24	.69 (17.5)	.75 (19.1)	.88 (22.4)	.94 (23.9)
28	.81 (20.6)	.87 (22.1)	1.00 (25.4)	1.08 (27.4)
32	.93 (23.6)	1.00 (25.4)	1.12 (28.4)	1.20 (30.5)
36	1.07 (27.2)	1.13 (28.7)	1.25 (31.8)	1.33 (33.8)
40	1.19 (30.2)	1.25 (31.8)	1.37 (34.8)	1.45 (36.8)
44	1.32 (33.5)	1.38 (35.0)	1.50 (38.1)	1.58 (40.1)
48	1.45 (36.8)	1.50 (38.1)	1.63 (41.4)	1.71 (43.4)
52	1.58 (40.1)	1.63 (41.4)	1.76 (44.7)	1.84 (46.7)
56	1.70 (43.2)	1.75 (44.5)	1.88 (47.8)	1.96 (49.8)

STANDARD SHIPPING PACKAGE/3		
DASH NO	MAX LENGTH PER PKG	
09 & 12	200 FT (60 m)	
16 THRU 52	100 FT (30 m)	

REVISIONS			
SYM.	DESCRIPTION	DATE	APPROVED
A	RELEASED	08/20/02	MP
B	REVISED PER DCN #20075	11/12/02	DM.
C	REVISED PER DCN #20210	12/17/02	KB
D	REVISED PER DCN #20725	04/22/03	DM.
E	REVISED PER DCN #36954	10/15/10	ACM
F	REVISED PER DCN #47957	09/23/13	ACM

EXAMPLE: 120 - 126 - 16 R

PRODUCT SERIES

BASIC NO

DASH NO, TABLE I

COLOR OPTION

BL = BLUE

R = RED

Y = YELLOW

TN = DESERT TAN

(OMIT FOR STD. BLACK)

PART NUMBER DEVELOPMENT

LENGTH

(AS SPECIFIED IN P.O.)

SPLIT

NOTES:

1. IDENTIFY WITH MANUFACTURERS NAME AND P/N.

2. METRIC DIMENSIONS (IN PARENTHESES) ARE GIVEN FOR REFERENCE ONLY, AND ARE BASED UPON 1 INCH = 25.4 mm.

3. UNLESS OTHERWISE SPECIFIED, CONDUIT WILL BE SHIPPED PER STANDARD PACKAGE MIN LENGTH SUPPLIED WILL BE 10 FEET (3m) WITH A MAX OF 4 LENGTHS PER PKG.

4. CONSULT FACTORY FOR AVAILABILITY OF INDICATED SIZE.

5. MATERIAL/FINISH:

CONVOLUTED TUBING - KYNAR

THIS COPYRIGHTED DOCUMENT IS THE PROPERTY OF GLENAIR, INC. AND IS FURNISHED ON THE CONDITION THAT IT IS NOT TO BE DISCLOSED, REPRODUCED IN WHOLE OR IN PART, OR USED TO SOLICIT QUOTATIONS FROM COMPETITIVE SOURCES, OR USED FOR MANUFACTURE BY ANYONE OTHER THAN GLENAIR, INC. WITHOUT WRITTEN PERMISSION FROM GLENAIR, INC. THE INFORMATION HEREIN HAS BEEN DEVELOPED AT GLENAIR'S EXPENSE AND MAY BE USED FOR ENGINEERING EVALUATION AND INCORPORATION INTO TECHNICAL SPECIFICATIONS AND OTHER DOCUMENTS WHICH SPECIFY PROCUREMENT OF PRODUCTS FROM GLENAIR, INC.

UNLESS OTHERWISE SPECIFIED

DIMENSIONS ARE IN INCHES

TOLERANCES:

FRACTIONS + 1/16

DECIMALS + .XX .03

ANGLES + 2°

DO NOT SCALE THIS DRAWING

B/F 02-1837 P/C 12

NON REPAIRABLE COMMERCIAL ITEM

DRAWN MP 08/20/02

CHECK MP 08/20/02

ENGR MP 08/20/02

RELEASE DATE 08/27/02

ORIGINAL RELEASE DATE 08/27/02

GLENAIR, INC.

1211 AIR WAY - GLENDALE - CALIFORNIA 91201

TUBING, CONVOLUTED, ANNULAR, SPLIT

CODE IDENT. NO. SIZE

06324 C 120-126 F

REV.

CAD 1987

SCALE N/A

WEIGHT N/A

SHEET 1 OF 1

1 of 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[120-126-24BL](#) [120-126-48BL](#) [120-126-16](#) [120-126-16R](#) [120-126-40](#) [120-126-16BL](#) [120-126-14BL](#) [120-126-09](#)
[120-126-12](#) [120-126-20BL](#) [120-126-48](#) [120-126-20](#) [120-126-14](#) [120-126-20R](#) [120-126-32BL](#) [120-126-40BL](#) [120-](#)
[126-09BL](#) [120-126-32](#) [120-126-52](#) [120-126-24](#) [120-126-28](#) [120-126-52BL](#) [120-126-12BL](#) [120-126-16Y](#) [120-126-](#)
[28BL](#)